



Connectors > Automotive Connectors > Connector Housings > Heavy Duty Sealed Connector Series Housings



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **1.6 mm, 2.8 mm** [ .059 in, .11 in ]

Connector System: **Wire-to-Wire**

Number of Positions: **16**

Centerline (Pitch): **4 mm, 6 mm** [ .157 in, .236 in ]

[All Heavy Duty Sealed Connector Series Housings \(186\)](#)

Features

Product Type Features

Connector & Housing Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	16
Number of Rows	2

Electrical Characteristics

Operating Voltage	60 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V, 60 V



Body Features

Cable Exit Angle	Other
Body Material	PBT GF
Primary Product Color	Black
Connector Code	03

Contact Features

Contact Size	1.5K, 2.8mm
Mating Tab Width	1.6 mm, 2.8 mm[.059 in][.11 in]
Contact Current Rating (Max)	40 A

Mechanical Attachment

Mounting Feature	Without
Terminal Position Assurance	Yes
Strain Relief	No
Mating Alignment Type	Keyed
Mating Alignment	With

Housing Features

Centerline (Pitch)	4 mm, 6 mm[.157 in][.236 in]
--------------------	------------------------------

Dimensions

Product Width	25.7 mm[1.012 in]
Product Length	67.2 mm[2.646 in]
Product Height	31.25 mm[1.23 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features



Packaging Quantity	230
Packaging Method	Box

Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 964972-1  
EINZELLEITERDICHTNG



TE Part # 828905-1  
SINGLE-WIRE-SEAL(5MM HOLE)



TE Part # CAT-H3399-B128  
Heavy Duty Sealed Connector Series Backshells



TE Part # 2112303-1  
PROTECTION CAP, FOR REC.HSG GROUP E




TE Part # CAT-AM705-T273  
AMP MCP, RECEPTACLE AND TAB




TE Part # CAT-H3399-CH8172  
Heavy Duty Sealed Connector Series Housings


Also in the Series | Heavy Duty Sealed Connector Series




Automotive Connector Caps & Covers (23)



Automotive Housings(193)



Automotive Seals & Cavity Plugs(5)



Other Automotive Connector Accessories(22)

Customers Also Bought



TE Part #DT04-12PA-CL11  
DEUTSCH DT Series Housings & Connectors



TE Part #3-1718324-1  
1.5/2.8MM TAB HSG.,62POS.,ASSY



TE Part #4-1563759-1  
Heavy Duty Sealed Connector Series Housings



TE Part #776536-2  
AS 16, 4P CAP ASSY, RD, KEY 2



TE Part #2500034-6  
SRC Female Conduit Cover



TE Part #SMBR-02-U  
DIN72585 BACKSHELL 90

TE Part #3-962352-1  
10P MESSERLEIS-GEH



TE Part #1-1437713-4  
106102=GROMMET WHITE



Documents

Product Drawings

16POS, MIXED,REC HSG,ASSY

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_3-1564337-1\_J.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1564337-1\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1564337-1\_J.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HDSCS Catalog

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English