



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (1.5% in 74025566) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 601966-1
[CRIMPING TOOL M22520/2-01](#)

Customers Also Bought



TE Part #204517-2
[AMPLIMITE,ASY,PLUG,STD,90,3](#)




TE Part #1053635-1
[2081 0000 02](#)




TE Part #2-1625999-0
[HSC100 22R 5%](#)



TE Part #1393766-5
[R10-E1X2-V185=R10](#)




TE Part #1061023-1
[5864 5001 10,OSX RA PCB JACK](#)



TE Part #207253-2
[RECEPT ASSY,9 POSN,AMPLIMITE](#)



TE Part #1-208778-1
[AMPLIMITE,SKT CONT,SZ 20](#)



TE Part #218542-002
[22759/34-24-9](#)



TE Part #YDTS26F15-19SBV001
[PLUG ASSY](#)



TE Part #392221-000
[DK-621-0412-USCS2682](#)

Documents

[Product Drawings](#)
[ARINC SIZE 15 SOCKET](#)
English

[CAD Files](#)
[3D PDF](#)
3D
Customer View Model
[ENG_CVM_CVM_226781-1_F.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_226781-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_226781-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1308940_Sec4_arinc600](#)

English

[ARINC 600 Next Generation Receptacle Connector](#)

English

Product Specifications

[Product Specification](#)

English

[COAXICON Contacts for use in RM or RME Connectors](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[AMP* COAXICON* CONTACTS FOR USE IN RM \(ARINC SPEC. 404\) OR RME \(MIL-C-](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[ARINC 404 RACK-AND-PANEL CONNECTORS SERIES R, RM, RME, M, MM, MME](#)

English