




Product: GDML 2011 LED 230 YE black

DIN Valve Connector, Form A, Field Attachable, 2+Ground, PG 11, Translucent Housing, with LED, 250 V

Product Description

GDM - 175301-803 (DIN 43650), Form A, Female, 18mm, Translucent Housing, 2+Ground (Protective Earth). screw contacts, PCB with Yellow LED, 230 AC/DC, 8A, black cable gland PG11 thread

Technical Drawing




MЗ

27.5

Central Screw Torque value: [50-60] Ncm





Technical Specifications

Technical Data

Product Family:	Valve Connectors				
Product Sub Family:	GDM Legacy				
Brand:	Hirschmann				
Connector Type:	Field Attachable				
Type of Contact / Gender:	Female				
Connector Design:	Angled				
Number of Pins:	2+PE (PE across cable outlet)				
Coding:	A				
Shielding:	Unshielded				
Attachment Type:	Central Screw				
Rated Voltage:	250 V				
Rated Impulse Voltage:	4.0 kV (PCBA 2.0 kV)				
Rated Current*:	8 A				
Contact Resistance:	≤ 10 mOhm				
Insulation Resistance:	> 10^9 Ohm				
Mating Cycles:	< 50				
Cable Gland:	PG11				
Conductor Cross Section:	0.25 - 1.5 mm ²				
Suitable Cables:	Ø 6 - 9 mm				

Ambient Temperature (Operation)*:	-40 °C - +80 °C		
Protection Degree / IP Rating**:	IP65		
Design Standard:	DIN EN 175301-803-A, ISO 4400		
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)		
Clearance / Creepage Distance:	DIN EN 60664-1 (2008/01); VDE 0110-1		
Overvoltage Category: III acc. to DIN EN 60664-1 (VDE 0110-1)			

Materials

Contact Base Material:	CuZn
Contact Plating:	Cu/Sn
Contact Bearer Color:	Black
Flammability Class (Contact Bearer):	UL 94 HB
Housing Color:	Translucent
Flammability Class (Housing):	UL 94 HB
Cable Gland Material:	PA GF
Cable Gland Gasket:	NBR
Cable Gland Color:	Black
Attachment Material:	Steel, Philips combi slot
Gasket Material:	Sold separately

Protection Circuitry

Function Indicator:	Yellow LED
Additional Technical Data	

Fastening Torque (Contact Screw): (40-50) Ncm for conductor size 0.25 - 1.5 mm ² ; (30-40) Ncm for conductor size 0.34 mm ² ; (25-30) Ncm for conductor size 0.25 m			
Fastening Torque (Cable Gland):	(250-375) Ncm		
Fastening Torque (Attachment):	(50-60) Ncm		

Approvals

VDE:	Yes
SEV:	Yes

Safety & Environmental Compliance

RoHS Compliant:	Yes
Notos	

Notes

Note Derating:	Notice derating
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connector.

Variants

Item #	Item Description	Central Screw	Gasket	Packaging	Replaced By
933739212	GDML 2011 LED 230 YE black	1- Steel Screw, Combi Head	0 - Sold Separately	D - Collect packaging 50 pieces, assembled	ID: 934888142 Name: GDM21FB-L1Y-10D

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulators based on their individual usage of the product.