



Product data sheet

Power tools for trade & industry

Cordless Impact Driver

PRO GDR 12V-110



Most compact impact driver in Bosch's 12 V category - with brushless motor

The most important data

Battery voltage	12.0 V
Torque, max.	110 Nm
No-load speed	0-1,200 rpm

Part Number 0 601 9E0 002

Technical data

Technical data

No-load speed	0-1,200 rpm
No-load speed (1st level)	0-1,200 rpm
No-load speed (2nd level)	0-2,600 rpm
Torque settings	2
Torque, max.	110 Nm
Impact rate	0-3,100 bpm
Impact rate (1st level)	0-2,700 bpm
Impact rate (2nd level)	0-3,100 bpm
Battery voltage	12.0 V
Tool holder	1/4" Hex Uni
Packaging dimensions (width x length x height)	215 x 335 x 80 mm
Weight incl. battery	0.9 kg

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	10 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Appropriate for conventional cordless impact driver applications due to 110 Nm of powerful torque
- Compactness ensures perfect handling, even in the tightest spaces and overhead
- For greater accuracy while screwdriving, 2-stage Power Control prevents the overtightening of small screws



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

