




MBC41-14-14-A

Ruland MBC41-14-14-A, 14mm x 14mm Bellows Coupling, Aluminum, Clamp Style, 41.3mm OD, 50.8mm Length



Description

Ruland MBC41-14-14-A is a bellows coupling with 14mm x 14mm bores, 41.3mm OD, and 50.8mm length. It is zero-backlash and has a balanced design for reduced vibration at high speeds. MBC41-14-14-A is comprised of two anodized aluminum hubs and a stainless steel bellows. The bellows are able to flex while remaining rigid under torsional loads allowing for all types of misalignment to be accommodated. This bellows coupling is lightweight and has low inertia making it suitable for applications with speeds up to 10,000 RPM. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. Ruland manufactures MBC41-14-14-A to be torsionally rigid and an excellent fit for precise positioning stepper servo applications as well as encoders. It is machined from solid bar stock that is sourced exclusively from North American mills and RoHS2 and REACH compliant. MBC41-14-14-A is carefully manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Large Bore B1	14 mm	Small Bore B2	14 mm
B1 Shaft Penetration	24.0 mm	B2 Shaft Penetration	24.0 mm
Outer Diameter OD	41.3 mm	Bore Tolerance	+0.03 mm / -.00 mm
Length L	50.8 mm	Hub Width LH	18.05 mm
Forged Clamp Screw	M4	Screw Material	Alloy Steel
Hex Wrench Size	3.0 mm	Screw Finish	Black Oxide
Seating Torque	4.6 Nm	Number of Screws	2 ea
Static Torque	28.0 Nm	Angular Misalignment	2.0°
Dynamic Torque Non-Reversing	14.00 Nm	Parallel Misalignment	0.25 mm
Dynamic Torque Reversing	7.00 Nm	Axial Motion	0.50 mm
Torsional Stiffness	63 Nm/Deg	Maximum Speed	10,000 RPM
Material Specification	Hubs: 2024-T351 Aluminum Bar Bellows: Type 321 Stainless Steel	Temperature	-40°F to 200°F -40°C to 93°C
Finish Specification	Sulfuric Anodized MIL-A-8625 Type II, Class 2 and ASTM B580 Type B Black Anodize	Country of Origin	USA
Weight (lbs.)	0.3050	UPC	63452906409
Note 1	Stainless steel hubs are available upon request.		
Note 2	Torque ratings are at maximum misalignment.		
Note 3	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 4	Torque ratings for the couplings are based on the physical limitations/failure point of the metal bellows. Under normal/typical conditions the hubs are capable of holding up to the rated torque of the metal bellows. In some cases, especially when the smallest standard bores are used or where shafts are undersized, slippage on the shaft is possible below the rated torque of the metal bellows. Keyways are available to provide additional torque capacity in the shaft/hub connection when required. Please consult technical support for more assistance.		