




Datasheet RS Pro

ENGLISH

Toroidal Transformers – Single Primary, Dual Secondary, Encapsulated

Specifications:

High quality encapsulated toroidal transformers with a single 230V/50-60Hz primary winding.
Twin secondary windings may be connected in series or parallel or used independently.



RS Code No.	Power [VA]	Full Load Vsec [V]	Rated Current per Sec [A]	No Load Vsec [V]	Case Diameter [mm]*	Case Height [mm]	Approx. Weight [kg]
1234007	15	2 x 6	1.25	2 x 7.02	63	35	0.3
1234008	15	2 x 9	0.83	2 x 10.42	63	35	0.3
1234009	15	2 x 12	0.63	2 x 13.89	63	35	0.3
1234010	15	2 x 25	0.30	2 x 29.07	63	35	0.3
1234011	30	2 x 6	2.50	2 x 7.17	82	39	0.45
1234012	30	2 x 9	1.67	2 x 10.65	82	39	0.45
1234013	30	2 x 12	1.25	2 x 14.19	82	39	0.45
1234014	30	2 x 15	1.00	2 x 17.71	82	39	0.45
1234015	30	2 x 25	0.60	2 x 29.75	82	39	0.45
1234016	50	2 x 6	4.17	2 x 6.80	87	42	0.65
1234017	50	2 x 9	2.78	2 x 10.20	87	42	0.65
1234019	50	2 x 12	2.08	2 x 13.71	87	42	0.65
1234020	50	2 x 15	1.67	2 x 17.22	87	42	0.65
1234021	50	2 x 25	1.00	2 x 28.78	87	42	0.65
1234022	80	2 x 12	3.33	2 x 13.60	104	44	0.9
1234023	160	2 x 15	5.33	2 x 16.63	115	53	1.5
1234025	160	2 x 25	3.20	2 x 27.31	115	53	1.5
1234026	225	2 x 12	9.38	2 x 13.14	126	52	1.9
1234027	225	2 x 15	7.50	2 x 16.32	126	52	1.9
1234028	225	2 x 25	4.50	2 x 27.42	126	52	1.9
1234029	300	2 x 35	4.29	2 x 37.88	126	65	2.3
1234031	500	2 x 25	10.00	2 x 26.71	148	65	3.5
1234032	500	2 x 30	8.33	2 x 32.27	148	65	3.5
1234033	500	2 x 35	7.14	2 x 37.47	148	65	3.5
1234034	500	2 x 40	6.25	2 x 43.03	148	65	3.5
1234035	500	2 x 45	5.56	2 x 48.60	148	65	3.5
1234036	500	2 x 55	4.55	2 x 58.61	148	65	3.5

Temperature Class Winding Wire : Class H (180°C), Insulation between windings : Class B (130°C)
Connection lead insulation : Class A (105°C)

Standards Designed, manufactured and tested according to the requirements of:
UL506 & UL5085-1, EN61558-1 Class II, EN60065 Class II