





RCJO50-XL

Flanged housing unit

Housing units RCJO, four-bolt flanged housing units, cast iron, eccentric locking collar, series 63, R seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
----------	----	----------------

Main Dimensions & Performance Data

d	50 mm	Bore diameter
L	175 mm	Flange width
U	70.1 mm	Total height unit
C _r	62,000 N	Basic dynamic load rating, radial
C _{0r}	38,000 N	Basic static load rating, radial
C _{ur}	1,800 N	Fatigue load limit, radial
≈m	4.7 kg	Weight

Mounting dimensions

J	132 mm	Distance fixing bore
N	23 mm	Fixing bore
n	4	Number of screwing holes



Dimensions

A	42.5 mm	Height housing
A ₁	19 mm	Thickness of flange
A ₂	28 mm	Distance raceway
V	144 mm	Shoulder diameter housing
Q	M6	Connection thread for lubrication
d ₃	75.8 mm	Outside diameter locking device

Additional information

1	Number of housings
CJO10	Housing
GNE50-XL-KRR-B	Bearing designation

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.