





1		2		3		4		5		6																																																																
A		 																																																																								
B																																																																										
C																																																																										
D		<table><tr><td colspan="2">part no.</td><td rowspan="2">ØD</td><td colspan="2">wire gauge</td><td rowspan="2">stripping length</td><td rowspan="2">Recommended Hand Crimp Tool</td><td rowspan="2">Note</td></tr><tr><td>silver plated</td><td>gold plated</td><td>mm²</td><td>AWG</td></tr><tr><td>09 15 000 6107*</td><td>09 15 000 6127*</td><td>0,90</td><td>0,14-0,37</td><td>26-22</td><td rowspan="6">8</td><td>09 99 000 0888 09 99 000 0001</td><td>*only for four indent crimping tool</td></tr><tr><td>09 15 000 6104</td><td>09 15 000 6124</td><td>0,90</td><td>0,14-0,37</td><td>26-22</td><td>09 99 000 0110 09 99 000 0021</td><td></td></tr><tr><td>09 15 000 6103</td><td>09 15 000 6123</td><td>1,10</td><td>0,5</td><td>20</td><td>09 99 000 0888</td><td></td></tr><tr><td>09 15 000 6105</td><td>09 15 000 6125</td><td>1,30</td><td>0,75</td><td>18</td><td>09 99 000 0001</td><td></td></tr><tr><td>09 15 000 6102</td><td>09 15 000 6122</td><td>1,45</td><td>1</td><td>18</td><td>09 99 000 0110</td><td></td></tr><tr><td>09 15 000 6101</td><td>09 15 000 6121</td><td>1,75</td><td>1,5</td><td>16</td><td>09 99 000 0021</td><td></td></tr><tr><td>09 15 000 6106</td><td>09 15 000 6126</td><td>2,25</td><td>2,5</td><td>14</td><td>6</td><td>09 99 000 0888 09 99 000 0001</td><td></td></tr></table>										part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note	silver plated	gold plated	mm²	AWG	09 15 000 6107*	09 15 000 6127*	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool	09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22	09 99 000 0110 09 99 000 0021		09 15 000 6103	09 15 000 6123	1,10	0,5	20	09 99 000 0888		09 15 000 6105	09 15 000 6125	1,30	0,75	18	09 99 000 0001		09 15 000 6102	09 15 000 6122	1,45	1	18	09 99 000 0110		09 15 000 6101	09 15 000 6121	1,75	1,5	16	09 99 000 0021		09 15 000 6106	09 15 000 6126	2,25	2,5	14	6	09 99 000 0888 09 99 000 0001	
		part no.		ØD	wire gauge		stripping length	Recommended Hand Crimp Tool	Note																																																																	
		silver plated	gold plated		mm²	AWG																																																																				
		09 15 000 6107*	09 15 000 6127*	0,90	0,14-0,37	26-22	8	09 99 000 0888 09 99 000 0001	*only for four indent crimping tool																																																																	
		09 15 000 6104	09 15 000 6124	0,90	0,14-0,37	26-22		09 99 000 0110 09 99 000 0021																																																																		
09 15 000 6103	09 15 000 6123	1,10	0,5	20	09 99 000 0888																																																																					
09 15 000 6105	09 15 000 6125	1,30	0,75	18	09 99 000 0001																																																																					
09 15 000 6102	09 15 000 6122	1,45	1	18	09 99 000 0110																																																																					
09 15 000 6101	09 15 000 6121	1,75	1,5	16	09 99 000 0021																																																																					
09 15 000 6106	09 15 000 6126	2,25	2,5	14	6	09 99 000 0888 09 99 000 0001																																																																				
		All Dimensions in mm Original Size DIN A4		Scale 2:1		Free size tol.		Ref.																																																																		
		All rights reserved Department EL PD		Created by hollert		Inspected by riepe		Standardisation		Date 03-Jul-2024																																																																
HARTING D-32339 Espelkamp				Title Han D crimp contacts male						State 40 - Released																																																																
				Type TB		Design Number DS00179341		SAP Mat. Number 09150006101		Rev. D																																																																
										Page 1/1																																																																