

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : RTD LIQUID
UFI : D1A0-30EW-U008-TA5R

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Lubricants, Greases and Release Products

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Reproductive toxicity, Additional category, Effects on or via lactation H362
Hazardous to the aquatic environment — Acute Hazard, Category 1 H400
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS09

Signal word (CLP) :

: Warning

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Contains	: C14-C17 CHLORINATED PARAFFIN
Hazard statements (CLP)	: H362 - May cause harm to breast-fed children. H400 - Very toxic to aquatic life.
Precautionary statements (CLP)	: P260 - Do not breathe dusts or mists. P263 - Avoid contact during pregnancy and while nursing. P280 - Wear protective gloves, protective clothing, eye protection, face protection. P308+P313 - IF exposed or concerned: Get medical advice/attention. P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.
EUH-statements	: EUH066 - Repeated exposure may cause skin dryness or cracking. EUH208 - Contains TERPINEOL(8000-41-7). May produce an allergic reaction.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
C14-C17 CHLORINATED PARAFFIN	CAS-No.: 85535-85-9 EC-No.: 287-477-0 EC Index-No.: 602-095-00-X REACH-no: 01-2119519269-33	≥ 70	Lact., H362 Aquatic Acute 1, H400 (M=100) Aquatic Chronic 1, H410
TERPINEOL	CAS-No.: 8000-41-7 EC-No.: 232-268-1 REACH-no: 01-2119553062-49 / 01-2119982324-34	0.1 – 1	Flam. Liq. 3, H226 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Skin Sens. 1, H317 Asp. Tox. 1, H304 Aquatic Chronic 2, H411

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No additional information available

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters. Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Obtain special instructions before use. Avoid contact during pregnancy/while nursing. Do not breathe dust/fume/gas/mist/vapours/spray. Avoid breathing dust/fume/gas/mist/vapours/spray.
Hygiene measures : Do not eat, drink or smoke when using this product. Wash hands, forearms and face thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

No additional information available

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1. National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:
Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:
Chemical goggles or safety glasses

8.2.2.2. Skin protection

Hand protection:
Wear protective gloves.

8.2.2.3. Respiratory protection

Respiratory protection:
Wear appropriate mask

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Consumer exposure controls:
Avoid contact during pregnancy/while nursing.

Other information:
Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: brown.
Odour	: Characteristic odour.
Odour threshold	: No data available
pH	: No data available.
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: > 100 °C

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Auto-ignition temperature	: > 200 °C
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available.
Relative density	: 1.1
Solubility	: insoluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: ≈ 110 mm ² /s
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

VOC content : 0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

C14-C17 CHLORINATED PARAFFIN (85535-85-9)

LD50 oral rat	> 4000 mg/kg bodyweight Animal: rat
LD50 dermal rabbit	> 13500 mg/kg bodyweight Animal: rabbit

TERPINEOL (8000-41-7)

LD50 oral rat	> 2000 mg/kg
LD50 dermal rat	> 2000 mg/kg

Skin corrosion/irritation : Not classified
pH: No data available.

Additional information : Repeated exposure may cause skin dryness or cracking.

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Serious eye damage/irritation	: Not classified pH: No data available.
Additional information	: Based on available data, the classification criteria are not met
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: May cause harm to breast-fed children.
Additional information	: May cause harm to breast-fed children.
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met

C14-C17 CHLORINATED PARAFFIN (85535-85-9)

NOAEL (oral, rat, 90 days)	100 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)
----------------------------	---

Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met

RTD LIQUID

Viscosity, kinematic	≈ 110 mm ² /s
----------------------	--------------------------

Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met
---	--

SECTION 12: Ecological information

12.1. Toxicity

Ecology - water	: Very toxic to aquatic life with long lasting effects.
Hazardous to the aquatic environment, short-term (acute)	: Very toxic to aquatic life.
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

C14-C17 CHLORINATED PARAFFIN (85535-85-9)

LC50 - Fish [1]	> 10000 mg/l Test organisms (species): Alburnus alburnus
LC50 - Fish [2]	> 5000 mg/l Test organisms (species): Alburnus alburnus
EC50 - Crustacea [1]	0.0059 mg/l Test organisms (species): Daphnia magna
EC50 - Other aquatic organisms [1]	0.006 mg/l
EC50 72h - Algae [1]	> 3.2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
EC50 96h - Algae [1]	> 3.2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
LOEC (chronic)	0.018 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC (chronic)	0.01 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC chronic fish	4.5 mg/l Test organisms (species): Oncorhynchus mykiss (previous name: Salmo gairdneri) Duration: '60 d'

12.2. Persistence and degradability

RTD LIQUID

Persistence and degradability	May cause long-term adverse effects in the environment.
-------------------------------	---

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

12.3. Bioaccumulative potential

RTD LIQUID

Bioaccumulative potential : Not established.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations






13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 3082	UN 3082	UN 3082	UN 3082	UN 3082
14.2. UN proper shipping name				
ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.	Environmentally hazardous substance, liquid, n.o.s.	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.
Transport document description				
UN 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (C14-C17 CHLORINATED PARAFFIN), 9, III, (-)	UN 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (C14-C17 CHLORINATED PARAFFIN), 9, III, MARINE POLLUTANT	UN 3082 Environmentally hazardous substance, liquid, n.o.s. (C14-C17 CHLORINATED PARAFFIN), 9, III	UN 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (C14-C17 CHLORINATED PARAFFIN), 9, III	UN 3082 ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (C14-C17 CHLORINATED PARAFFIN), 9, III
14.3. Transport hazard class(es)				
9	9	9	9	9
				
14.4. Packing group				
III	III	III	III	III

RTD LIQUID

Safety Data Sheet


according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADR	IMDG	IATA	ADN	RID
14.5. Environmental hazards				
Dangerous for the environment: Yes	Dangerous for the environment: Yes Marine pollutant: Yes	Dangerous for the environment: Yes	Dangerous for the environment: Yes	Dangerous for the environment: Yes
No supplementary information available				

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: M6
Special provisions (ADR)	: 274, 335, 375, 601
Limited quantities (ADR)	: 5I
Excepted quantities (ADR)	: E1
Packing instructions (ADR)	: P001, IBC03, LP01, R001
Special packing provisions (ADR)	: PP1
Mixed packing provisions (ADR)	: MP19
Portable tank and bulk container instructions (ADR)	: T4
Portable tank and bulk container special provisions (ADR)	: TP1, TP29
Tank code (ADR)	: LGBV
Vehicle for tank carriage	: AT
Transport category (ADR)	: 3
Special provisions for carriage - Packages (ADR)	: V12
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV13
Hazard identification number (Kemler No.)	: 90
Orange plates	:



Tunnel restriction code (ADR)	: -
EAC code	: •3Z

Transport by sea

Special provisions (IMDG)	: 274, 335, 969
Limited quantities (IMDG)	: 5 L
Excepted quantities (IMDG)	: E1
Packing instructions (IMDG)	: LP01, P001
Special packing provisions (IMDG)	: PP1
IBC packing instructions (IMDG)	: IBC03
Tank instructions (IMDG)	: T4
Tank special provisions (IMDG)	: TP1, TP29
EmS-No. (Fire)	: F-A
EmS-No. (Spillage)	: S-F
Stowage category (IMDG)	: A

Air transport

PCA Excepted quantities (IATA)	: E1
PCA Limited quantities (IATA)	: Y964
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 964
PCA max net quantity (IATA)	: 450L
CAO packing instructions (IATA)	: 964
CAO max net quantity (IATA)	: 450L
Special provisions (IATA)	: A97, A158, A197
ERG code (IATA)	: 9L

Inland waterway transport

Classification code (ADN)	: M6
---------------------------	------

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Special provisions (ADN)	: 274, 335, 375, 601
Limited quantities (ADN)	: 5 L
Excepted quantities (ADN)	: E1
Equipment required (ADN)	: PP
Number of blue cones/lights (ADN)	: 0

Rail transport

Classification code (RID)	: M6
Special provisions (RID)	: 274, 335, 375, 601
Limited quantities (RID)	: 5L
Excepted quantities (RID)	: E1
Packing instructions (RID)	: P001, IBC03, LP01, R001
Special packing provisions (RID)	: PP1
Mixed packing provisions (RID)	: MP19
Portable tank and bulk container instructions (RID)	: T4
Portable tank and bulk container special provisions (RID)	: TP1, TP29
Tank codes for RID tanks (RID)	: LGBV
Transport category (RID)	: 3
Special provisions for carriage – Packages (RID)	: W12
Special provisions for carriage - Loading, unloading and handling (RID)	: CW13, CW31
Colis express (express parcels) (RID)	: CE8
Hazard identification number (RID)	: 90

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 0 g/l

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

For the following substances of this mixture a chemical safety assessment has been carried out:

C14-C17 CHLORINATED PARAFFIN

SECTION 16: Other information

Data sources	: REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.
Other information	: None.

RTD LIQUID

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Full text of H- and EUH-statements	
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment — Chronic Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Lact.	Reproductive toxicity, Additional category, Effects on or via lactation
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H362	May cause harm to breast-fed children.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
EUH066	Repeated exposure may cause skin dryness or cracking.
EUH208	Contains TERPINEOL(8000-41-7). May produce an allergic reaction.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.