


## FEATURES

- **Metal Detectable:** Enhances safety by allowing detection in food and pharmaceutical processing environments.
- **Nylon Material:** Provides durability and resistance to wear, ensuring long-lasting performance.
- **385 mm Length:** Suitable for bundling larger cables or multiple wires together.
- **Tensile Strength of 15 kg:** Offers robust holding power for secure fastening.
- **UL 94HB Fire Behaviour:** Meets fire safety standards, reducing risk in high-temperature environments.
- **RoHS Compliant:** Ensures adherence to environmental and safety regulations.

## RS PRO Metal Detectable Cable Tie, 385 mm Length

RS Stock No: 656-080



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO metal detectable cable ties are designed for secure bundling and fastening of cables and wires, particularly in environments where metal detection is crucial. Ideal for use in the food and pharmaceutical industries, they help prevent contamination and ensure compliance with safety standards.

### General Specifications

Colour	Blue
Product Type	Cable Tie
Sub Type	Metal Detectable
Tensile Strength	15 kg

### Protection Category

Fire Behaviour	UL 94HB
UV Resistant	No

### Mechanical Specifications

Length	385 mm
Material	Nylon
Maximum Bundle Diameter	110 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------

