



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 7:59 (UTC)



22312EAE4

Spherical Roller Bearings

Boundary Dimensions

d	60	mm	Bore diameter
D	130	mm	Outside diameter
B	46	mm	Width
r (min.)	2.1	mm	Chamfer dimension

Basic Load Ratings

Cr	340000	N	Basic dynamic load rating
C0r	340000	N	Basic static load rating

Speeds

Thermal Speed Rating (Oil-bath)	4000	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	5600	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	3600	min-1	Grease lubrication
Oil (Oil-bath)	4500	min-1	Oil-bath lubrication

Abutment and Fillet Dimensions

da (min.)	72	mm	Diameter of shaft abutment
da (max.)	79	mm	Diameter of shaft abutment
Da (min.)	111	mm	Diameter of housing abutment
Da (max.)	118	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors

e	0.34	Constant
Y2	3	Axial load Factors
Y3	2	Axial load Factors
Y0	1.9	Axial load Factors

Mass

Mass approx.	2.89	kg	Mass approx.
--------------	------	----	--------------

