

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Cordless Band Saw

GCB 18V-127



The powerful band saw with brushless motor for high-depth, fast, and nearly spark-free cuts in metal

The most important data

Battery voltage	18.0 V
Weight excl. battery	6.45 kg

Part Number 0 601 2B7 000

Technical data

Technical data

Weight excl. battery	6.45 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	237 x 542 x 318 mm
BITURBO	No

Noise/vibration information

Sawing metal

Vibration emission value ah	1.5 m/s ²
Uncertainty K	1.5 m/s ²



Product data sheet

Power tools for trade & industry

Advantages:

- Powerful brushless motor for fast cuts and high cutting capacity up to 127 x 127 mm
- Designed for your comfort with low vibrations and almost spark-free cutting in metal
- LED-light, different speed modes, and a material guide give you control for cleaner cuts and more accuracy

