

Product Code: 01-1083BA

Product Type: 50cm x 40m Chemical Absorbent Roll

Fabric: Spun bond/Melt blown polypropylene

Range: Classic

Brand: Lubetech

Width (cm): 50

Length (cm): 4000

Pack Quantity: 1

Construction: SMS

Comp. GSM:

Total GSM:

Colour MB: Yellow

Colour SB: Yellow

Finish Dimpled: Yes

Finish Perforated: Yes

Pack Weight (kg):

Pack Weight (lbs):


Inline perf dimensions (cm): 19/19

Cross perf dimensions (cm): 40

Type: Hydrophilic

Packaging type: Box

Packaging code:



Features / Benefits:

- Yellow colour code signals emergency use
- The sorbent is made up of two layers that are sonically welded together.
- Top layer is made of a no-lint, durable spun-bond polypropylene.
- Core/base layer is made from high loft melt blown fibres.
- Not as slippery as a fully laminated absorbent.

Additional Information

Basis weights and recycled content are +/- 5%

Images are provided for illustration purposes only and actual product may vary

Measures absorbency utilising BS 7959-1 2004 / ASTM 726 (long test) with medium viscosity oil and tap water. Statistical average delivered from real time production QC data

Date/version: 16|08|2019 v1.0