

## PT Ratchet lever hoist

### Capacity 800 - 6300 kg

Ratchet lever hoists PT features improved techniques and ergonomical styling. The advantages of the predecessor range have been maintained and further optimized. A good, versatile, all round ratchet lever hoist for demanding conditions.

### Features

- The proven stamped steel housing provides extremely low weight without limiting the reliability and sturdiness of the unit.
- The short handle lever is fitted with an ergonomic rubber grip.
- Standard free chaining device to quickly attach the load or to pull the chain through the hoist in both directions.
- Alloyed steel link chain with zinc-plated resp. yellow chromated finish, in accordance with national and international standards and regulations.
- Forged suspension and load hooks are made from non-aging, high tensile steel and fitted with robust safety latches.

### Option

- All models can be equipped with an overload protection device in the form of a slip clutch which is factory preset to approx. 25% ± 15% overload.



## INFO

All ratchet lever hoists with a capacity exceeding 750 kg can be used for load attachment according to EN 12195.

Yale hoists and trolleys are not designed for passenger elevation applications and must not be used for this purpose.



Option:  
Overload protection device

## Technical data PT

Model	Art.-No.	Capacity kg	Number of chain falls	Chain dimensions d x p in mm/ design	Lift with one full lever turn mm	Handle pull at WLL daN	Weight at standard lift (1.5 m) kg
PT 800	N02200005	800	1	5.6 x 17.1 - T	24	26	5.5
PT 1600	N02200006	1600	1	7.1 x 21.2 - T	23	30	9.6
PT 3200	N02200007	3200	1	9 x 27.2 - V	16	38	16.0
PT 6300	N02200008	6300	2	9 x 27.2 - V	8	39	31.0

## Dimensions PT

Model	PT 800	PT 1600	PT 3200	PT 6300
A min., mm	290	330	430	580
B, mm	21	27	36	53
C, mm	24	31	35	46
D, mm	13	20	24	43
E, mm	235	370	370	370
F, mm	120	138	177	259
G, mm	38	41	53	85
H, mm	82	97	124	174
J, mm	142	163	185	185
K, mm	52	65	83	83
L, mm	90	98	102	102

