



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Hardware



Circular Connector Hardware Type: **Cable Fitting**

Accepts Cable Diameter Range: [.394 – .748 in]

Features

Product Type Features

Product Type	Accessory
Circular Connector Hardware Type	Cable Fitting

Body Features

Material	Metal
----------	-------

Mechanical Attachment

Screw & Hole Thread Size	PG21
--------------------------	------

Dimensions

	.394 – .748 in
--	----------------

Packaging Features

Packaging Quantity	5
Packaging Method	Box

Other

Comment	Includes 2 pressure rings and cut-out sealing ring
---------	--

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224)




Candidate List Declared Against: JUN 2016
(169)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Customers Also Bought




TE Part #Y5015-000000077958
WIRE SEAL GROMMET - CIRP




TE Part #2176407-8
3560 27K 1%




TE Part #Y5015-000000004245
FIXED, REAR MOUNT SOCKET CONNECTOR



TE Part #EC9902-000
ZHD-SCE-1K-12.7-50-9



TE Part #1888972-3
Cage Assy PCI Hsink LP QSFP Thru Bezel



TE Part #1969605-2
2P PM PLUG VAL-U-LOK PM GW

Documents

Product Drawings
DS.21.DI
English



CAD Files

Customer View Model

[ENG_CVM_CVM_4-1106004-9_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_4-1106004-9_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-1106004-9_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.