

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through



1670727

<https://www.phoenixcontact.com/gb/products/1670727>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



QUICKON panel feed-through, for external panel mounting with manual solder/slip-on connection, 2.8 x 0.8 mm, 3-pos.

## Commercial data

Item number	1670727
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AF6HAA
Product key	AF6HAA
Catalog page	Page 16 (PC-2002)
GTIN	4017918156961
Weight per piece (including packing)	16.79 g
Weight per piece (excluding packing)	16.27 g
Customs tariff number	85369010
Country of origin	PL

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through

1670727

<https://www.phoenixcontact.com/gb/products/1670727>

## Technical data

### Product properties

Product type	Panel feed-through
Number of positions	3
Position marking	1, 2, 3
Number of connections	3
Number of connections per position	1
Shielded	no

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Connection data


#### Connection technology

Connection method On the device side	Manual solder/slip on connection
Connection method On the field side	IDC connection
Frequency of connections between conductors of the same cross section	10 (if the conductor is connected more than once, seal and cap may need to be replaced.)

#### Conductor connection

Conductor cross section flexibel	0.34 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
Conductor cross section solid	0.34 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
Connection cross section AWG	18 ... 16
Tightening torque Union nut	2.5 Nm
Tightening torque Contact carrier	3.75 Nm
Tightening torque Locking nut	3.75 Nm
Wrench size Union nut	19 mm
Wrench size Contact carrier	19 mm

### Dimensions

Dimensional drawing	
Width	19 mm
Height	19 mm
Length	41.3 mm

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through



1670727

<https://www.phoenixcontact.com/gb/products/1670727>

## Electrical properties

Rated surge voltage (III/3)	4 kV
Contact resistance	< 3 mΩ
rated voltage (II/2)	320 V (with insulating sleeve)
rated voltage (III/2)	160 V (with insulating sleeve)
Rated voltage (III/3)	160 V (with insulating sleeve)
Nominal voltage $U_N$	160 V AC
	160 V DC
Nominal current $I_N$	9 A

## Material specifications

Color (Housing)	green (RAL 6021)
Material Housing	PA
Material Contact	Cu alloy
Material Contact surface	Sn
Flammability rating according to UL 94	V0
Material wire insulation	PVC / PE

## Cable/line

Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	Class 2-6 // 0.34 mm <sup>2</sup> : 0.1 mm; 0.5 - 0.75 mm <sup>2</sup> : 0.15 mm
Wire diameter including insulation	2.5 mm
Position marking	1, 2, 3

## Mounting

Mounting type	Front mounting Pg9
Assembly note	If the conductor is reconnected, it must be cut off above the last contact point. QUICKON components may only be operated when under no load.

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Impact strength	IK06
Ambient temperature (operation)	-25 °C ... 80 °C (Specifications of the cable manufacturer must be observed.)
	-25 °C ... 50 °C (when the conductor is connected. Specifications of the cable manufacturer must also be observed.)
Temperature when conductor connected	-5 °C ... 50 °C

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through


1670727

<https://www.phoenixcontact.com/gb/products/1670727>



## Drawings

### Dimensional drawing



# Q 0,75/3FL/9-9KU-ESA - Panel feed-through





1670727


<https://www.phoenixcontact.com/gb/products/1670727>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1670727>

 <b>cUL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	6 A	-	-

 <b>UL Recognized</b> Approval ID: E118976				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	9 A	-	-

 <b>EAC</b> Approval ID: RU C-DE.A*30.B.01102	
--	--

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through



1670727

<https://www.phoenixcontact.com/gb/products/1670727>

## Classifications

### ECLASS

ECLASS-13.0

27440602

### ETIM

ETIM 9.0

EC002566

### UNSPSC

UNSPSC 21.0

39121500

# Q 0,75/3FL/9-9KU-ESA - Panel feed-through



1670727

<https://www.phoenixcontact.com/gb/products/1670727>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.0 Climate Change

CO2e kg	0.104 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)