



40Vmax Multi Tool XGT®

TM001G

10,000 - 20,000 min⁻¹

Model TM001G is a cordless multi tool powered by a 40Vmax XGT® Li-Ion battery and designed to be compatible with STARLOCK MAX accessories.

Combination of high work efficiency and low vibration. Low vibration achieved by Anti Vibration Technology (AVT). Features and benefits: Constant speed control, Variable speed control, 12 angle settings of accessory at every 30° from 0° to 360°, Tool-less accessory clamp, LED job light, Soft start.



Technical specifications

Nominal Battery Voltage	40 V
Orbits per Minute	10000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,8 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding	≤ 2,5 m/s ²
Tool weight with battery	2,1 - 3,3 kg
Product Dimensions (L x W x H):	332 x 92 x 138 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Voltage XGT	✓
Product net weight	1,4 kg
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Vibration Level, Cutting With Plunge Cut Saw Blade	≤ 2,5 m/s ²

User benefits

- Tool-less blade change for fast blade installation and removal
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Built-in LED light with afterglow function illuminates the work area
- Soft start for smooth start-ups
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Anti-restart function minimises accidental start-up
- Brushless maintenance-free and long-life motor
- 12 Angle settings at every 30° from 0° to 360°

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing