


■ GEBERIT



Example image

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120\text{ }^{\circ}\text{C}$
- For saturated steam $\leq 120\text{ }^{\circ}\text{C}$
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5

- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

Product material	CrNiMo steel 1.4401 (EN 10088)
------------------	--------------------------------

Art. no.	DN	d, ø mm	R "	L cm	H cm
33009	10 / 15	12	1/2	3.6	1.9
31726	12 / 10	15	3/8	3.8	1.8
31703	12 / 15	15	1/2	4.1	2.1
31714	12 / 20	15	3/4	4.3	2.3

Art. no.	DN	d _ø mm	R _e	L cm	H cm
31704	15	18	1/2	4.2	2.2
31705	15 / 20	18	3/4	4.4	2.4
31715	20 / 15	22	1/2	4.2	2.1
31707	20	22	3/4	4.4	2.3
31716	20 / 25	22	1	4.6	2.5
31717	25 / 20	28	3/4	4.6	2.3
31708	25	28	1	4.8	2.3
31718	25 / 32	28	1 1/4	4.8	2.5
31719	32 / 25	35	1	5.1	2.5
31709	32	35	1 1/4	5.3	2.7
31720	32 / 40	35	1 1/2	5.3	2.7
31721	40 / 32	42	1 1/4	5.7	2.7
31710	40	42	1 1/2	5.7	2.7

Art. no.	DN	d _ø mm	R _e	L cm	H cm
31722	50 / 40	54	1 1/2	8.3	4.8
31711	50	54	2	8.9	5.4
31713	65	76.1	2 1/2	11.9	7
31724	80	88.9	3	13.7	7.7