

FEATURES

- Fix input unregulated single output
- Continuous short-circuit protection.
- •
- Compact SMD package
- Industry standard pin-out
- I/O isolation test voltage 1.5KVDC
- No-load input current as low as 8mA
- Operating temperature range - 40°C to +105°C
- High efficiency up to 83%
- IEC62368, UL62368, EN62368 approved

RS PRO 1W isolated DC-DC converters

- **2233668, 2233670, 2233671,**
- 2233673, 2233676, 2233679



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

PCB Mount DC-DC converters are specially designed for applications where an isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits. Featuring continuous short circuit protection and no-load input current as low as 8mA

General Specifications

Model	DC-DC 1W Isolated DC-DC converter
Mounting Type	PCB SMD
MTBF	MIL-HDBK-217F@25°C > 3,500,000 hrs
Applications	Industrial control systems, instrumentation, analog, relay-driven and data switching circuits.

	Input Voltage	(Vdc)	Output	Output		Max. Capacitive	Efficiency
RS Stock#	Nominal	Max	Voltage	Current Max/Min	Wattage	Load(µF)	(Тур)
2233668			5V	200/20mA	1W	2400	82%
2233670	12V		12V	83/9mA	1W	560	83%
2233671	(10.8-13.2	2)	15V	67/7	1W	560	83%
2233673	_		24V	42/5mA	1W	220	81%
2233676	24V		5V	200/20mA	1W	2400	80%
2233679	(21.6-26.4	1)	12V	83/9mA	1W	560	80%



Input Specifications

Input Specification						
Item	Operating Con	ditions	Min.	Тур.	Max.	Unit
		5VDC output	-	102/8	107/	
	12VDC input	12VDC and 15VDC output		101/8	106/	
Input Current (full load / no-load)		24V output	-	99/8	103/	
	24)/DC in sut	5VDC output	-	53/8	57/	mA
	24VDC input	12VDCoutput	-	51/8	55/	
Reflected Ripple Current	Nominal input	voltage	-	15	-	
Surge Valtage (1000 may)	12VDC input		-0.7	-	18	VDC
Surge Voltage (1sec. max.)	24VDC input		-0.7	-	30	VDC
Input Filter				Capacitanc	e Filter	
Hot Plug				Unavaila	able	

Output Specifications

Output Specification							
Item	Operating Co	nditions	Min	Тур.	Max	Unit	
Voltage Accuracy			See out	See output regulation curves (Fig. 1)			
Linear Regulation	Input voltage	change: ±1%	-	-	1.2	-	
		5VDC output	-	5	15		
	10% -100% load	12VDC output		3	10	0/	
Load Regulation		15VDC output		3	10	%	
		24VDC output	-	2	10		
Temperature Coefficient	100% load		-	±0.02	-	%/°C	
Ripple & Noise *	20MHz	5VDC/12VDC & 15VDC output	-	30	75	mV p-p	
	bandwidth	24VDC output		50	100		
Short circuit Protection			Co	ntinuous,	self-recov	ery	
Note: * The "parallel cable Application Notes for spec		sed for ripple and noise test, n.	olease refer	to DC-DC	Converter		



General Specifications


Item	Operating Conditions	Min	Тур	Max.	Unit
Isolation	Input-output Electric Strength Test for 1 minute with a leakage current of 1mA max.	1500	-	-	VDC
Insulation Resistance	Input-output resistance at 500VDC	1000	-	-	MΩ
Isolation Capacitance	Input-output capacitance at 100KHz/0.1V		20		pF
Operating Temperature	Derating when operating temperature≥100°C, (see Fig. 2)	-40	-	+105	°C
Storage Temperature		-55	-	+125	
Case Temperature Rise	Ta=25°C	-	25	-	
Storage Humidity	Non-condensing	5	-	95	%RH
Reflow Soldering Temperature*			temp.≤24 tion time≤	-	
Vibration		10-150H	z, 5G, 0.75 Z a	5mm. alon axis	g X,Y and
Switching Frequency	Full load, nominal input voltage	-	260	-	KHz
MTBF	MIL-HDBK-217F@25°C		3500		K hours
Note:*For actual application	on, please refer to IPC/JEDEC J-STD-020D.1.				

EMC Specifications

Facialisma	CE	CISPR32/EN55032 CLASS B	
Emissions	RE	CISPR32/EN55032 CLASS B	
Immunity	ESD	IEC/EN61000-4-2 Air ±8kV, Contact ±6kV perf.	Perf. Criteria B
Note: Refer to Fig	g.4 for recommended cir	cuit test	



Typical Performance Curves





Design Reference

Typical application

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig.3. Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer to Table 1.





Fig.3

Table 1 : Recommended input and output capacitor values

Vin	Cin	Vout	Cout
12VDC	2.2μF/25V	5VDC	10µF/16V
24VDC	1μF/50V	12VDC	2.2μF/25V
		15VDC	1µF/25V
		24VDC	1µF/50V

EMC compliance circuit




	C1	4.7μF /50V
	C2	4.7μF /50V
Emissions	CY	270pF/2kV
	C3	Refer to the Cout in table 1
	LDM	6.8µH



Mechanical Specifications

Case material	Black plastic; flame-retardant and heat-resistant (UL94 V-0)
Dimensions	13.20 x 11.40 x 7.25 mm
Weight	1.4g (Тур.)
Cooling Method	Free air convection

Dimensions and recommended layout



Unit: mm[inch] Pin section tolerances: ±0.10[±0.004] General tolerances: ±0.25[±0.010]

THIRD ANGLE PROJECTION

1

Note: Grid 2.54*2.54mm

Pir	n-Out
Pin	Function
1	GND
2	Vin
4	OV
5	+Vo
8	NC

NC: Pin to be isolated from circuitry

Approvals

Safety Certification

IEC62368, UL62368, EN62368 approved



- 1. If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet.
- 2. The maximum capacitive load offered were tested at input voltage range and full load.
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity
- 4. Our products shall be classified according to ISO14001 and related environmental laws and regulations.