

Jig Saw LXT®

DJV185

18V, 23 mm, 800 – 3 000 min⁻¹

Model DJV185 is a barrel handle type cordless jig saw powered by 18V LXT® Li-Ion battery

Features and Benefits: 3 orbital settings + straight cutting, Variable Speed Control, Toolless blade clamp, Barrel handle.



LXT **BL** **SOFT**
MOTOR NO LOAD

Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Brushless Motor	✓
Strokes per Minute (SPM)	800 - 3000 min ⁻¹
Length of Stroke	23 mm
Max. Cutting Capacity in Wood (90°)	135 mm
Max. Cutting Capacity in Steel (90°)	10 mm
Capacity Aluminium	20 mm
Orbital Action	✓
Tool weight with battery	2,0 - 2,3 kg
Product Dimensions (L x W x H):	259 x 77 x 183 mm
Max. Bevel Range (Left)	0 - 45 °
Vibration Level, Cutting Boards	10,3 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,7 m/s ²
Vibration Level, Cutting Sheet Metal	9,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Sheet Metal	1,5 m/s ²

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Lock-on feature for continuous operation
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Brushless motor provides high power and excellent cutting performance
- LED light illuminates the work site
- 3 orbital settings

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing