

# FOUR-POLE CONTACTOR, IEC OPERATING CURRENT ITH (AC1) = 25A, AC COIL 50/60HZ, 24VAC



Product designation		Power contactor
Product type designation		BF09
Contact characteristics		
Number of poles	nr.	3
Rated insulation voltage Ui	V	690
Rated impulse withstand voltage Uimp	kV	6
Operating frequency		
Operational frequency min	Hz	25
Operational frequency max	Hz	400
Conventional free air thermal current Ith	Α	25
Operating current		
Operational current AC3 (≤440V ≤55°C)	Α	9
Operational current AC4 (400V)	Α	4.9
Short-time allowable current for 10s (IEC/EN60947-1)	Α	150
Protection fuse		
gG (IEC)	Α	25
aM (IEC)	Α	10
Making capacity (RMS value)	Α	90
Breaking capacity at voltage		
Breaking capacity 440V	Α	72
Breaking capacity 500V	Α	72
Breaking capacity 690V	Α	71
Resistance per pole (average value)	mΩ	2.5
Power dissipation per pole (average value)		
Power dissipation pole (average value) Ith	W	1.6
AC3	W	0.2
Tightening torque for terminals		
min .	Nm	1.5
max	Nm	1.8
min	lbft	1.1
max	lbft	1.5
Tightening torque for coil terminal		
min	Nm	0.8
max	Nm	1
min	lbft	0.59
max	lbft	0.74
max number of wires simultaneously connectable	nr.	2
Conductor section		
AWG		
min		16
max		10
Flexible w/o lug conductor section		
min	mm²	1
max	mm²	6
Flexible c/w lug conductor section		



# FOUR-POLE CONTACTOR, IEC OPERATING CURRENT ITH (AC1) = 25A, AC COIL 50/60HZ, 24VAC

			•	
		min	mm²	1
		max	mm²	4
	Flexible with insulated spade lug conductor section			
		min	mm²	1
-		max	mm²	4
	tion according to IEC/EN 60529			IP20
Auxiliary contact chara	cteristics			
Type of contact				1 NA
Thermal current Ith			Α	25
IEC/EN 60947-5-1 des	signation			A600
Ambient conditions				
Temperature				
·	Operating temperature			
	-1	min	°C	-50
		max	°C	70
	Storage temperature	max		10
	Storago temperaturo	min	°C	-60
		max	°C	80
Max altitude		Παχ		
			m	3,000
Operating position				
		ormal		Vertical plan
=	allov	wable		±30°
Mounting				Screw / DIN rail
				35mm
Weight			g	0.367
Operations				
Mechanical life			Cycles	20,000,000
Electrical life			Cycles	2000000
Safety related data				
Performance level B10	0d according to EN/ISO 13489-1 -			
	Performance level B10d according to			
	Performance level B10d according to	EN/IS	88 <b>160 DOS</b>	-12010000100000000000000000000000000000
Mirror contats according	ng to IEC/EN 609474-4-1			Yes
EMC compatibility				Yes
AC coil operating				
Rated AC voltage at 50	)/60Hz, 60Hz			
Ü	,	min	V	12
		max	V	600
AC operating voltage			<u> </u>	
Je sporaming voltage	of 50/60Hz coil powered at 50Hz			
	pick-up			
	ριοκ-αρ	min	%Us	80
	drop cut	max	%Us	110
	drop-out		0/11-	20
		min	%Us	20
		max	%Us	55
	4-24-21			
	of 50/60Hz coil powered at 60Hz			
	of 50/60Hz coil powered at 60Hz pick-up			
		min	%Us	85
		min max	%Us %Us	85 110
	pick-up			
	pick-up	max	%Us	110





# FOUR-POLE CONTACTOR, IEC OPERATING CURRENT ITH (AC1) = 25A, AC COIL 50/60HZ, 24VAC


	of 60Hz coil powered at 60Hz			
	, pick-up			
	·	min	%Us	80
		max	%Us	110
	drop-out			
	·	min	%Us	20
		max	%Us	55
AC operating voltage				
	of 50/60Hz coil powered at 50Hz			
	•	in-rush	VA	75
		holding	VA	9
	of 50/60Hz coil powered at 60Hz	<u> </u>		_
	•	in-rush	VA	70
		holding	VA	6.5
	of 60Hz coil powered at 60Hz	<u> </u>		
		in-rush	VA	75
		holding	VA	9
Dissipation at holding :	≤20°C 50Hz		W	2.5
Max cycles frequency			•••	
Mechanical operations			Cycles/h	3 600
Operating times			C y oloo/11	0,000
Average time for Us co	ontrol			
Two rage time for 00 oc	in AC			
	Closing NO			
	Olosing NO	min	ms	8
		max	ms	24
	Opening NO	IIIdA	1113	24
	Opening NO	min	ms	10
		max	ms	20
	Closing NC	max	1110	20
	Globing No	min	ms	14
		max	ms	28
	Opening NC	max	1110	20
	Opening No	min	ms	7
		max	ms	, 18
UL technical data		тах	1110	10
	for three-phase AC motor			
	prisade i to motor	at 480V	Α	7.6
		at 600V	A	9
Yielded mechanical pe	erformance	αι σσσ ν		
. Iolada Modiambai pe	for single-phase AC motor			
	isi singic phase Ao motor	at 110/120V	hp	0.75
		at 110/120V	hp	2
	for three-phase AC motor	at 250 V	ıηγ	
	ioi tilico pilaso Ao Illotoi	at 200/208V	hp	3
		at 220/230V	hp	3
		at 460/480V	hp	5
		at 575/600V	hp	7.5
Contact rating of auxilia	ary contacts according to UL	at 373/000V	ıηγ	SI - A600
General USE	ary cornacts according to OL			01 - 7000
General USE	Contactor			
	Contactor	ΛΩ	۸	25
	Auvilian contacts	AC current	A	25
	Auxiliary contacts	A O	\/	000
		AC voltage	V	600




FOUR-POLE CONTACTOR, IEC OPERATING CURRENT ITH (AC1) = 25A, AC COIL 50/60HZ,

AC current A 10
DC voltage V 250
DC current A 1

### Dimensions



### Wiring diagrams



### Certifications and compliance

Certifications

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-4-1

UL 60947-1

UL 60947-4-1

Compliance

CCC

cULus

EAC

#### ETIM 6 classification





FOUR-POLE CONTACTOR, IEC OPERATING CURRENT ITH (AC1) = 25A, AC COIL 50/60HZ,

EC000066 - Power contactor, AC switching