



Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors



Connector & Housing Type: **Receptacle**

Connector System: **Board-to-Board**

Number of Positions: **36**

Centerline (Pitch): **1.27 mm [.05 in]**

Number of Rows: **2**

Features

Product Type Features

Shell Material Configuration	Full Metal Shell
Connector & Housing Type	Receptacle
Connector System	Board-to-Board
Connector Shell Size	2
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	36
Number of Positions	36
Number of Rows	2
PCB Mount Orientation	Right Angle

Body Features

Shield Plating Material	Nickel
Insert Material	PBT
Shield Material	Die Cast Metal
Shell Plating Material	Nickel
Mating Feature Material	Steel
Mating Feature Plating Material	Nickel
Primary Product Color	Black



Connector Profile	Standard
Contact Features	
Contact Underplating Material	Nickel
	30 µin
Contact Options	Installed
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Shape & Form	Rectangular
Contact Current Rating (Max)	1 A
Termination Features	
Rectangular Termination Post & Tail Width	.4 mm[.015 in]
Rectangular Termination Post & Tail Thickness	.32 mm[.012 in]
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	2.8 mm[.11 in]
Mechanical Attachment	
Mounting Feature Plating Material	Nickel
Mounting Feature Material	Zinc
Mounting Hole Diameter	2.7 mm
Mating Alignment Type	Integral with mating surface
PCB Mount Alignment	With
PCB Mount Retention	With
PCB Mount Retention Type	Retention Leg
Mating Retention	With
Mating Retention Type	Latch
Connector Mounting Type	Panel Mount & Board Mount
Housing Features	
Housing Material	Thermoplastic Polyester - Glass-Filled
Shell Material	Steel
Centerline (Pitch)	1.27 mm[.05 in]
Dimensions	
PCB Thickness (Recommended)	1.6 mm[.063 in]



Row-to-Row Spacing	1.9 mm[.075 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Shielded	No
Circuit Application	Signal

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Box & Tray, Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 4-2232346-1
SCSI .050 PLUG ASS'Y 36P

Also in the Series | SCSI Connectors



PCB D-Sub Connectors(10)




Solder D-Sub Connectors(10)

Customers Also Bought



TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING



TE Part #6162-213-1677
CONT SOC ASSY



TE Part #917251-2
DYNAMIC D-3400F HDR ASSY 20P H



TE Part #1-2834497-6
MINI DYNAMIC REC HSG ASSY 16P Y-KEY BLK



TE Part #CAT-D9934-A15B
Receptacle and Tab Housing: 2.5 mm Pitch, 250V



TE Part #1-1437624-7
PKA90B1/4=KNOB PLASTIC 1/4 IN



TE Part #CAT-D9934-A15A
DYNAMIC 1100 REC AND TAB HSG

Documents

Product Drawings
SCSI .050 REC ASS'Y 36P PB-FREE

English

CAD Files



3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2232516-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2232516-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2232516-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

CHAMP.050 Series(II) Connector Wire to Board Type

English

Product Specification

English