


**06800030**

RCK 80 - Self centring

**2D Technical Drawing**

**Dynamic 3D View**
**Technical Specifications**

|  |          |
|--|----------|
| Part number (CODE)                                   | 06800030 |
| Ød (DD) mm   | 30       |
| ØD (D) mm  | 41       |
| D1 (D1) mm   | 57       |
| D2 (D2) mm   | 62       |
| L1 (L1) mm   | 25       |
| L2 (L2) mm   | 39.5     |
| L3 (L3) mm   | 46.5     |
| L (L) mm   | 52.5     |
| Maximum torque Mt (MT) Nm                            | 510      |
| Clamping pressure - Shaft (CPS) N/mm <sup>2</sup>    | 127      |
| Clamping pressure - Hub (CPH) N/mm <sup>2</sup>      | 90       |
| Clamping screws DIN 912 MAT. 12.9 - Num. (CSN)       | 6        |
| Clamping screws DIN 912 MAT. 12.9 - Type (CST)       | M6x18    |
| Clamping screws DIN 912 MAT. 12.9 - Torque (CSTQ) Nm | 17.0     |