







Turns ratio	1 + 1 to 2 + 2		
Weight	32g		
	Min.	Typ.	Max.
Primary DC resistance (per winding)	-15%	60Ω	+15%
Secondary DC resistance (per winding)	-15%	165Ω	+15%
Optimal source impedance (series)		600Ω	
LF -3dB point			10Hz
HF -3dB point *	25kHz	30kHz	
30Hz max level (3% THD)		+0dBm	
THD (0dBm, 1kHz)		0.005%	0.01%
THD (0dBm, @ 20Hz)		1.9%	





Tolerance on all dimensions +/-0.2mm unless stated otherwise
Pin diameter = 0.71mm

* With 600Ω source resistance, screen (pin 8) grounded.
Unused pins should be left floating with minimal pad size for best performance.
Fitted with screening can.



Walters OEP Ltd.
Unit 5, Oxonian Park, Langford Locks,
Kidlington, Oxfordshire. OX5 1FP
Tel: (01865) 855085 Fax: (01865) 855075
Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
PCB mounting line input transformer Impedance: 150Ω/600Ω to 600Ω/2.4kΩ page 1 of 2	1	23/07/07	CS		Z218A2C
	2	29/09/09	CS		
Scale: nts					
All dimensions in mm unless stated otherwise					



Walters OEP Ltd.
Unit 5, Oxonian Park, Langford Locks,
Kidlington, Oxfordshire. OX5 1FP
Tel: (01865) 855085 Fax: (01865) 855075
Website: www.oep.co.uk

DESCRIPTION	ISSUE	DATE	DRAWN	CHECKED	DRAWING NUMBER
PCB mounting line input transformer Impedance: 150Ω/600Ω to 600Ω/2.4kΩ page 2 of 2	1	23/07/07	CS		Z218A2C
	2	29/09/09	CS		
Scale: nts					
All dimensions in mm unless stated otherwise					