



APC Back-UPS, 1050VA/600W Floor/Wall Mount, 230V, 8x Schuko CEE 7/3 outlets, USB Type A+C Port, User Replaceable Battery

BE1050G2-GR

Overview

Lead time	Usually in Stock
Main	
Main Input Voltage	230 V
Other Input Voltage	220 V
Main Output Voltage	230 V
Other Output Voltage	220 V
Rated power in W	600 W
rated power in VA	1050 VA
Product or component type	Uninterruptible power supply (UPS)
Input Connection Type	Schuko CEE 7/7P
output connection type	6 Schuko CEE 7 2 Schuko CEE 7 surge
Battery type	Lead-acid battery
Provided equipment	User manual
Range of product	Back-UPS

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery charger power	7 W rated
Battery power in VAH	80 VAh runtime
Replacement battery	RBC17 ☐

General

Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

Physical

Height	40
neight	12 cm

Rates duty January 2016

Width	13 cm
Depth	36.5 cm
Net weight	4 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Network frequency	4763 Hz
Input voltage limits	180266 V
Maximum input current	6 A
Switching current capacity	10 A

Output

Maximum configurable power in W	600 W
Output frequency	4763 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
UPS type	Standby
Wave type	Stepped approximation to a sinewave
Efficiency	80 % (full load)
Graph start point	40
Maximum configurable power in VA	1050 VA

Conformance

Product certifications	CE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient air temperature for operation	040 °C
Relative humidity	090 %
Operating altitude	03000 ft
Ambient air temperature for storage	-1545 °C
Storage Relative Humidity	095 %
Storage altitude	0.0000000004572.0000000000 m
Acoustic level	45 dBA

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

control panel	LED status display with load and battery bar-graphs and on line : on battery : replace
	battery : and overload indicators

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	19 cm
Package 1 Width	44.1 cm
Package 1 Length	18.6 cm
Package 1 Weight	4.4 kg
SCC14	10731304738272

Contractual warranty

Warranty

2 years repair or replace, 3 years repair or replace for European Union countries



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	019b51cf-d7f1-4f06-ac85-1378fc94c7aa
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No

Product datasheet

BE1050G2-GR

Image of product / Alternate images

Alternative





