

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**SECTION 1: Identification of the substance/mixture and of the company/undertaking**

· **1.1 Product identifier**

· **Trade name: PC Bio 10**

· **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.

· **Application of the substance / the mixture** Detergent

· **1.3 Details of the supplier of the safety data sheet**

· **Manufacturer/Supplier:**

Alfred Kärcher GmbH & Co. KG  
Alfred-Kärcher-Str. 28-40  
D - 71364 Winnenden

Postfach 160  
D - 71349 Winnenden

Tel.: +49-7195-14-0  
Fax : +49-7195-14-2212

[www.karcher.com](http://www.karcher.com)

**Distributor:**  
Kaercher (UK) Ltd.  
Kaercher House  
Beaumont Road  
Banbury  
Oxon OX16 1TB  
Great Britain

Tel.: +44-1295-752-000  
Fax : +44-1295-266-436

· **Further information obtainable from:**

Department PCD-D  
Tel.: +49-7195-14-2548  
Fax : +49-7195-14-3164  
[safetydata@karcher.com](mailto:safetydata@karcher.com)

· **1.4 Emergency telephone number:**

For Hazardous Materials [or Dangerous Goods] Incidents  
Spill, Leak, Fire, Exposure, or Accident  
Call CHEMTREC Day or Night  
Within USA and Canada: 1-800-424-9300  
Outside USA and Canada: +1 703-741-5970 (collect calls accepted)

GB

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 1)

**SECTION 2: Hazards identification**

- **2.1 Classification of the substance or mixture**
  - **Classification according to Regulation (EC) No 1272/2008**  
The product is not classified according to the CLP regulation.

---

- **2.2 Label elements**
  - **Labelling according to Regulation (EC) No 1272/2008** Void
  - **Hazard pictograms** Void
  - **Signal word** Void
  - **Hazard statements** Void
  - **Additional information:**  
Safety data sheet available on request.
- **2.3 Other hazards**  
The product does not contain any organic halogen compounds (AOX), nitrates, heavy metal compounds.
- **Results of PBT and vPvB assessment**
  - **PBT:** Not applicable.
  - **vPvB:** Not applicable.

**SECTION 3: Composition/information on ingredients**

- **3.2 Chemical characterisation: Mixtures**
  - **Description:** Mixture of substances listed below with non-hazardous additions.
  - **Dangerous components:** Void
- **Regulation (EC) No 648/2004 on detergents / Labelling for contents**

non-ionic surfactants	<5%
-----------------------	-----
- **Additional information** For the wording of the listed hazard phrases refer to section 16.

**SECTION 4: First aid measures**

- **4.1 Description of first aid measures**
  - **General information** No special measures required.
  - **After inhalation** Supply fresh air; consult doctor in case of complaints.
  - **After skin contact** Rinse with warm water.
  - **After eye contact** Rinse opened eye for several minutes under running water.
  - **After swallowing**  
Rinse out mouth and then drink plenty of water.  
If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

GB

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 2)

### **SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents** Water with full jet.
- **5.2 Special hazards arising from the substance or mixture**  
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### **SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:**  
Dilute with plenty of water.  
Do not allow to penetrate the ground/soil.
- **6.3 Methods and material for containment and cleaning up:**  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders).  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
No dangerous substances are released.  
See Section 7 for information on safe handling  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### **SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling**  
No special measures required.  
Ensure good ventilation/exhaustion at the workplace.  
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Protect from frost.
- **7.3 Specific end use(s)** No further relevant information available.

### **SECTION 8: Exposure controls/personal protection**

- **Additional information about design of technical facilities:** No further data; see item 7.

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 3)

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**  
*The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.*
- **8.2 Exposure controls**
- **Personal protective equipment**
- **General protective and hygienic measures** *Do not inhale gases / fumes / aerosols.*
- **Respiratory protection:**  
*In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.  
Not necessary if room is well-ventilated.*
- **Protection of hands:**  
*Synthetic rubber gloves  
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.  
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation*
- **Material of gloves**  
*The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.*
- **Penetration time of glove material**  
*The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.*
- **For the permanent contact in work areas without heightened risk of injury (e.g. Laboratory) gloves made of the following material are suitable:**  
\* butyl rubber 0,7 mm, 480 min
- **As protection from splashes gloves made of the following materials are suitable:**  
\* nitril rubber 0,4 mm, 30 min
- **Eye protection:** *Goggles recommended during refilling.*

\*

**SECTION 9: Physical and chemical properties**

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

<b>Form:</b>	Fluid
<b>Colour:</b>	Colourless
<b>Odour:</b>	Specific type
<b>Odour threshold:</b>	Not determined.
- **pH-value at 20 °C:** 7
- **pH-value 1 %:** 7

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 4)

· <b>Change in condition</b> Melting point/freezing point: 0 °C Initial boiling point and boiling range: 100 °C	
· <b>Flash point:</b>	Not applicable
· <b>Flammability (solid, gaseous)</b>	Not applicable.
· <b>Ignition temperature:</b>	not applicable
· <b>Decomposition temperature:</b>	Not determined.
· <b>Auto-ignition temperature:</b>	Product is not selfigniting.
· <b>Explosive properties:</b>	Product does not present an explosion hazard.
· <b>Explosion limits:</b> Lower: Upper:	Not determined. Not determined.
· <b>Vapour pressure at 20 °C:</b>	23 hPa
· <b>Density at 20 °C:</b> · <b>Relative density</b> · <b>Vapour density</b> · <b>Evaporation rate</b>	1.017 g/cm <sup>3</sup> Not determined. Not determined. Not determined.
· <b>Solubility in / Miscibility with</b> Water:	Fully miscible
· <b>Partition coefficient: n-octanol/water:</b>	Not determined.
· <b>Viscosity:</b> dynamic at 20 °C: kinematic:	4 mPas Not determined.
· <b>Solvent content:</b> VOC (EC) Solids content:	0.00 % 4.2 %
· <b>9.2 Other information</b>	No further relevant information available.

**SECTION 10: Stability and reactivity**

- **10.1 Reactivity** corresponds to 10.3
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known

GB

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 5)

\*

### **SECTION 11: Toxicological information**

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### **SECTION 12: Ecological information**

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **Other information:** The product is biodegradable.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **COD-value:** 47000 mg/l
- **General notes:**  
The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.  
Generally not hazardous for water.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

### **SECTION 13: Disposal considerations**

- **13.1 Waste treatment methods**
- **Recommendation**  
Hand over to hazardous waste disposers.  
Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.
- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 6)

· **Recommended cleansing agents:** Water, if necessary together with cleaning agents.

**SECTION 14: Transport information**

· <b>14.1 UN-Number</b> · <b>ADR, ADN, IMDG, IATA</b>	Void
· <b>14.2 UN proper shipping name</b> · <b>ADR, ADN, IMDG, IATA</b>	Void
· <b>14.3 Transport hazard class(es)</b> · <b>ADR, ADN, IMDG, IATA</b> · <b>Class</b>	Void
· <b>14.4 Packing group</b> · <b>ADR, IMDG, IATA</b>	Void
· <b>14.5 Environmental hazards:</b> · <b>Marine pollutant:</b>	No
· <b>14.6 Special precautions for user</b>	Not applicable.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	Not dangerous according to the above specifications.
· <b>UN "Model Regulation":</b>	Void

**SECTION 15: Regulatory information**

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

**SECTION 16: Other information**

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship. A product information sheet can be provided if requested.*

- **Department issuing SDS:** PCD-D
- **Contact:**  
Department PCD-D  
Tel.: +49-7195-14-2548  
Fax : +49-7195-14-3164  
safetydata@karcher.com

(Contd. on page 8)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 02.02.2018

Version number 4

Revision: 01.08.2016

**Trade name: PC Bio 10**

(Contd. of page 7)

· **Abbreviations and acronyms:**

*ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)*

*IMDG: International Maritime Code for Dangerous Goods*

*IATA: International Air Transport Association*

*ELINECS: European Inventory of Existing Commercial Chemical Substances*

*ELINCS: European List of Notified Chemical Substances*

*CAS: Chemical Abstracts Service (division of the American Chemical Society)*

*VOC: Volatile Organic Compounds (USA, EU)*

*PBT: Persistent, Bioaccumulative and Toxic*

*vPvB: very Persistent and very Bioaccumulative*

· **\* Data compared to the previous version altered.**

· 0-011-636-0

PC Bio 10/1

1-951