


PGJ12 - Printing Materials - Component		P	LTR	DESCRIPTION	DATE	DWN	APVD
PGJ18 - Printing Materials Certified for Canada - Component			A	INITIAL RELEASE	17OCT2025	YB	SL
File: MH17292	Model N°: T2KP						

LABEL AND LINER DESIGN




LABELS PER ROLL: 10 000
LABELS ACROSS: 1

OUTSIDE WOUND

TE PN: 2483429-1

All dimensions in mm [INCHES]

PRESENTATION



**Packaging presentation
and specification on page 2**

	Kiss cut		Die cut
	Back slit		Adhesive cut
	Perforation		45° die cut
	2 kiss cut enductions		

Grid removed: Yes
Sales unit: The label

PRINTING			
	Color		Color
1	N.A.	5	
2		6	
3		7	
4		8	

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.2 [0.001]
LABEL WIDTH:	±0.2 [0.001]
WEB WIDTH:	±0.3 [0.012]
VERTICAL REPEAT:	±0.1 [0.001]
HORIZONTAL REPEAT:	±0.3 [0.012]
PRINT POSITIONING:	-
LEFT MARGIN:	±0.3 [0.012]
QUANTITY:	-0% + 2%
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

	DIMENSIONS:
	mm [inches]
* *	
MATERIAL	SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:		
0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

DWN	17OCT2021
Y. BONINO	
CHK	17OCT2021
D. BURGAT	
APVD	17OCT2021
S. LAZRAK	
PRODUCT SPEC	
TTDS-294	
APPLICATION SPEC	
-	
WEIGHT	0.045

5					TE Connectivity			
5								
5	NAME							
	Part Description							
	T2KP-508064-10-9-1AC							
	-							
	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
	A2	FB1U7	C=2483429-1	-				
	SCALE			NTS	SHEET		1	OF 2
							REV	A




1 splice max. per roll



TOLERANCES mm [INCHES]	
LABEL HEIGHT:	
LABEL WIDTH:	
WEB WIDTH:	
VERTICAL REPEAT:	
HORIZONTAL REPEAT:	
PRINT POSITIONING:	
LEFT MARGIN:	
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

MATERIAL				-
ADHESIVE TYPE				-
LINER				-
DWN	17OCT2025	MATERIAL	HEAT TREAT	
Y. BONINO		SEE TABLE		-
CHK	17OCT2025			-
Y. BONINO				
APVD	17OCT2025			
S. LAZRAK				
NAME		T2KP-508064-10-9-1AC		
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	2483429-1	2 OF 2	B

	A	INITIAL RELEASE	17OCT2025	YB	SL
P	LTR	REVISION RECORD	DATE	DWN	APV

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC	- ± ± ± ±
ANGLES	±	-	
SURFACE TEXTURE	-	✓	