

F202 AC-40/0,03

General Information

Extended Product Type: F202 AC-40/0,03

Product ID: 2CSF202001R1400

EAN: 8012542780106

Catalog Description: F202 AC-40/0,03 Residual Current Circuit Breaker

Long Description: The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Residual Current Devices RCDs » Residual Current Devices RCDs



Dimensions

Product Net Width:	0.035 m
Product Net Height:	0.085 m
Product Net Depth / Length:	0.069 m
Product Net Weight:	0.200 kg

Technical

Standards:	IEC/EN 61008 UL 1053
Operating Characteristic:	Instantaneous
Type of Residual Current:	AC type
Rated Residual Current:	30 mA
Rated Current (I _n):	40 A
Number of Poles:	2
Power Loss:	at Rated Operating Conditions per Pole 2.4 W
Rated Voltage (U _r):	230/400 V
Rated Frequency (f):	50...60 Hz

Environmental

Ambient Air Temperature:	Operation -25 ... +55 °C Storage -40 ... +70 °C
--------------------------	--

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Package Level 1 Height:	0.078 m
Package Level 1 Depth / Length:	0.096 m
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 EAN:	8012542780106

RoHS Status:	Following EU Directive 2011/65/EU
--------------	-----------------------------------

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	277 V AC
-----------------------------------	----------