

USB 3.1



Product Highlights:

- Exceptional durability in a stylish, lightweight design
- Built to withstand tough conditions—impact/pressure (up to 750 PSI), weather (-13°F to 300°F), and water (up to 98 ft) resistant
- Stores and transfers content quickly (up to 150MB/s read and 60MB/s write)*
- Simple plug-and-play design
- Compatible with PC and Mac® systems
- USB 3.1 compatible, backwards compatible with USB 3.0 and 2.0 devices
- Three-year limited warranty

Capacities:

- 32GB**
(up to 130MB/s read, 25MB/s write)
- 64GB**
(up to 150MB/s read, 60MB/s write)
- 128GB**
(up to 150MB/s read, 60MB/s write)



Tough. Fast. Secure.

Tough conditions have met their match with the Lexar® JumpDrive® Tough USB 3.1 flash drive. This stylish, lightweight drive provides the durability you need to know your content is safe. And with high-speed performance, it's one tough customer. So whether you work or play in harsh conditions, push your devices to the limit, or just want to protect against the bumps and bruises of everyday life, it's got you covered.

Made tough for life's challenges. With its rugged outer shell and stylish design, JumpDrive Tough stands up to life's challenges. It is impact and pressure resistant (up to 750 PSI), harsh weather resistant (-13°F to 300°F), and water resistant (up to 98 feet). It also includes an oversized attachment loop, so from keychain to carabiner, it's easy to take on the go.



750 PSI



-13°F to 300°F



98 ft



256-bit AES

Quickly transfer files. When it comes to moving content, who's got time to wait? The high-performance JumpDrive® Tough provides speeds up to 150MB/s read and 60MB/s write.* Quickly transfer a 3GB HD video clip in less than 1 minute, compared to the 4 minutes it takes using a standard USB 2.0 drive.** And for added versatility, the drive is backwards compatible with USB 3.0 and 2.0 devices.

With a long history in the industry, we know memory. We move quickly with technology to design the solutions you need, and work with device manufacturers to make sure our products are compatible. Then we stand behind them with outstanding warranties and helpful customer service. We're dedicated to performance, reliability, and expert support, so when it comes to storing the memories that matter, trust Lexar.

For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and storage drives. With so many options, it's easy to find the right Lexar solution to fit your needs.

*Up to 150MB/s read transfer, write speeds lower. Speeds based on internal testing. Actual performance may vary. x=150KB/s.

**Based on 64GB capacity. 3.2GB video, HD 1080p@30fps (46 Mbps) video.

Impact/pressure, temperature (storage), and water resistance specifications based on internal testing with included cap on. Actual performance may vary.

Security safeguards, by their nature, are capable of circumvention. Lexar does not guarantee data will be 100% secure from unauthorized access, alteration, or destruction.

NOTE: The latest USB driver is recommended for best performance. Contact your device manufacturer to ensure compatibility before installing. Some of the listed storage capacity is used for formatting and other purposes and is not available for data storage. 1GB equals 1 billion bytes.

www.lexar.com

©2018 Lexar International. All rights reserved. Information, products, and/or specifications are subject to change without notice. Lexar is responsible for omissions or errors in typography or photography. Lexar and the Lexar Logo are trademarks or registered trademarks. All other trademarks are the property of their respective owners.