



SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 1

Compilation date: 02/03/20

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Product code: 47000-47009

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Line Marking Paint

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Aerosol 1: H222; -: H229

Most important adverse effects: Extremely flammable aerosol. Pressurised container: May burst if heated.

2.2. Label elements

Label elements:

Hazard statements: H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

Hazard pictograms: GHS02: Flame



Signal words: Danger

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 2

P251: Do not pierce or burn, even after use.

P410+P412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P271: Use only outdoors or in a well-ventilated area.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

DIMETHYL ETHER

EINECS	CAS	PBT / WEL	CLP Classification	Percent
204-065-8	115-10-6	Substance with a Community workplace exposure limit.	Flam. Gas 1: H220; Press. Gas: H280	10-20%

O-XYLENE

202-422-2	95-47-6	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Skin Irrit. 2: H315	3.0-10%
-----------	---------	---	---	---------

ACETONE - REACH registered number(s): 01-2119471330-49

200-662-2	67-64-1	-	Flam. Liq. 2: H225; Eye Irrit. 2: H319; STOT SE 3: H336; -: EUH066	3.0-10%
-----------	---------	---	--	---------

1-METHOXY-2-PROPANOL - REACH registered number(s): 01-2119457435-35-XXXX

203-539-1	107-98-2	-	Flam. Liq. 3: H226; STOT SE 3: H336	3.0-10%
-----------	----------	---	-------------------------------------	---------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Seek medical attention if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Delayed / immediate effects: No data available.

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 3

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid. Mark out the contaminated area with signs and prevent access to unauthorised personnel.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 4

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

DIMETHYL ETHER

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	766 mg/m3	958 mg/m3	-	-

O-XYLENE

EU	221 mg/m3	442 mg/m3	-	-
----	-----------	-----------	---	---

ACETONE

UK	1210 mg/m3	3620 mg/m3	-	-
----	------------	------------	---	---

1-METHOXY-2-PROPANOL

UK	375 mg/m3	560 mg/m3	-	-
----	-----------	-----------	---	---

DNEL/PNEC Values

Hazardous ingredients:

ACETONE

Type	Exposure	Value	Population	Effect
DNEL	Dermal	186	Workers	Local
DNEL	Inhalation	2420	Workers	Local
DNEL	Oral	62	Consumers	Systemic
PNEC	Fresh water	10.6	-	-
PNEC	Marine water	1.06	-	-
PNEC	Soil (agricultural)	33.3	-	-
PNEC	-	-	-	-

8.2. Exposure controls

Engineering measures: The floor of the storage room must be impermeable to prevent the escape of liquids.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses.

Skin protection: Protective clothing.

Environmental: No data available

Section 9: Physical and chemical properties

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 5

9.1. Information on basic physical and chemical properties

State: Aerosol	
Colour: Various	
Odour: Characteristic odour	
Evaporation rate: Fast	
Oxidising: No data available.	
Solubility in water: Miscible	
Viscosity: No data available.	
Boiling point/range°C: No data available.	Melting point/range°C: No data available.
Flammability limits %: lower: No data available.	upper: No data available.
Flash point°C: -30	Part.coeff. n-octanol/water: No data available.
Autoflammability°C: No data available.	Vapour pressure: No data available.
Relative density: No data available.	pH: No data available.
VOC g/l: No data available.	

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 6

Hazardous ingredients:

O-XYLENE

IPR	MUS	LD50	1550	µl/kg
ORL	RAT	LDLO	5	gm/kg

ACETONE

IVN	RAT	LD50	5500	mg/kg
ORL	MUS	LD50	3	gm/kg
ORL	RAT	LD50	5800	mg/kg

1-METHOXY-2-PROPANOL

IVN	RAT	LD50	4200	mg/kg
ORL	MUS	LD50	11700	mg/kg
ORL	RAT	LDLO	3739	mg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Delayed / immediate effects: No data available.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

ACETONE

BLUEGILL (<i>Lepomis macrochirus</i>)	LC50	8300	mg/l
---	------	------	------

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 7

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: No data available

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

14.2. UN proper shipping name

Shipping name: AEROSOLS

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

Packing group: n/a

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D

Transport category: 2

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Transport in bulk: Not Applicable

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

[cont...]

SAFETY DATA SHEET

EASYLINE EDGE - ALL COLOURS - (FROM 09.03.2020)

Page: 8

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.

H220: Extremely flammable gas.

H222: Extremely flammable aerosol.

H225: Highly flammable liquid and vapour.

H226: Flammable liquid and vapour.

H229: Pressurised container: May burst if heated.

H312: Harmful in contact with skin.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H336: May cause drowsiness or dizziness.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.