

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, laser-inscribed to customer specifications, pliers and properties as in CRIMPFOX CENTRUS 10H

## Your advantages

- Pressure lock ensures consistently high quality crimping results
- Ergonomic handle design ensures comfortable, fatigue-free handling
- With a particularly small handle width, the tool fits perfectly in your hand
- Up to 30 % lower actuation force, thanks to optimized leverage
- Ideal for TWIN ferrule
- Sturdy plastic guard over the head of the pliers protects the tool against damage caused by dropping

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1213176                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BH3                            |
| Product key                          | BH313V                         |
| Catalog page                         | Page 475 (C-3-2019)            |
| GTIN                                 | 4055626212654                  |
| Weight per piece (including packing) | 468.1 g                        |
| Weight per piece (excluding packing) | 330.85 g                       |
| Customs tariff number                | 82032000                       |
| Country of origin                    | SE                             |

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

## Technical data

### Notes

|                                  |                                                                                                               |
|----------------------------------|---------------------------------------------------------------------------------------------------------------|
| General                          | DIN 46228-1, DIN 46228-4                                                                                      |
| Environmental Product Compliance |                                                                                                               |
| California Proposition 65        | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |

### Product properties

|              |               |
|--------------|---------------|
| Product type | Crimping tool |
| Compression  | HEX crimp     |

#### Crimping position 1

|                    |                      |
|--------------------|----------------------|
| Min. cross section | 0.14 mm <sup>2</sup> |
| Max. cross section | 10 mm <sup>2</sup>   |
| AWG min            | 26                   |
| AWG max            | 8                    |

### Connection data

#### Conductor connection

|                             |                                             |
|-----------------------------|---------------------------------------------|
| Cross section range, metric | 0.14 mm <sup>2</sup> ... 10 mm <sup>2</sup> |
| Cross section range AWG     | 26 ... 8                                    |

### Dimensions

|        |        |
|--------|--------|
| Width  | 70 mm  |
| Height | 21 mm  |
| Length | 180 mm |

### Material specifications

|       |             |
|-------|-------------|
| Color | black/green |
|-------|-------------|

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1213176>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 21043811 |
| ECLASS-12.0 | 21043811 |
| ECLASS-13.0 | 21043811 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000168 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

# CRIMPFOX CENTRUS 10H CUS - Crimping pliers



1213176

<https://www.phoenixcontact.com/in/products/1213176>

## Accessories

### CRIMPFOX/ SPR-4 - Replacement spring

1200288

<https://www.phoenixcontact.com/in/products/1200288>

Spare recuperating spring



---

### CRIMPFOX CENTRUS NC/U-HANDLE - Replacement handle

1202880

<https://www.phoenixcontact.com/in/products/1202880>

Replacement upper handle for CRIMPFOX CENTRUS series



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)