

Sapphire Nano Foam+

Ultra-thin high cut resistant glove with nitrile foam coating

Outstanding level of cut protection and tactility on the thinnest liner possible. With a nitrile foam coated palm, the second skin feeling has never been better to work in oily and wet conditions.

Features

- ▲ High cut resistance: Level F / A7
- ▲ 21 gauge seamless liner offers unprecedented level of fingertip sensitivity for precision tasks
- ▲ Durable nitrile foam palm coating ensures good protection against oily and wet parts
- ▲ Reinforced thumb crotch enhances durability
- ▲ Touchscreen capabilities to allow usage with screen devices
- ▲ Designed for easy movement and continuous wear
- ▲ Breathable back of hand to reduce perspiration
- ▲ Seamless knit prevents irritation

Certifications



Suitable industries & applications

Industries

- ▲ Automotive
- ▲ Construction
- ▲ Manufacturing
- ▲ Facilities Management

- ▲ Utilities
- ▲ Highways and Infrastructure

Applications

- ▲ Machinery and Plant Operation
- ▲ Component and Product Assembly
- ▲ Vehicle Repairs and Maintenance
- ▲ Handling Sharp or Abrasive Materials



Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Sapphire Nano Foam+

Ultra-thin high cut resistant glove with nitrile foam coating

Product information

Materials	Liner:	21 Gauge Engineered HPPE, Tungsten, Nylon, HPPE
	Coating:	Foam Nitrile
Colour	Grey / Black	
Length	210mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

XS	SKG00079FB	Items per Pack 10 x Pairs
S	SKG00079FD	
M	SKG00079FF	Items per Case 120 x Pairs
L	SKG00079FH	
XL	SKG00079FJ	
XXL	SKG00079FL	

Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.