



Product data sheet

Power tools for trade & industry

HGS 65/50

INDUSTRIAL HGS 65/50



Straight handle, offset drive end for polishing bit with low circumferential speed with flap discs with diameters up to 80 mm

The most important data

Permitted grinding stone diameter	50 mm
No-load speed	4,700 rpm
Rated power, output	630 W

Part Number 0 602 210 434

Technical data

Technical data

Frequency	300 Hz
Voltage	200 V
Permitted grinding stone diameter	50 mm
No-load speed	4,700 rpm
Rated power, input	900 W
Rated power, output	630 W
Rated current	3.3 A
Weight as per EPTA	2.8 kg
Toolholder, drive end	Collet 6 mm
Switch version	Safety switch

Product data sheet

Power tools for trade & industry



BOSCH
Invented for life

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

