

Drg No :- C 44607


SPECIFICATION

ACTUATING FORCE :- 5.0N(18ozf)MAX
 RELEASE FORCE :- 1.7N(6.0ozf)MIN
 FREE POSITION :- 50.0 (1.97) MAX
 OPERATING POSITION :- $47.6^{+1.5}$ (1.87)
 MOVEMENT DIFFERENTIAL :- 1.2 (0.05)MAX
 OVERTRAVEL (AVAILABLE) :- 12.1(0.48)



SPECIAL FEATURE :-
 TESTED AND STAMPED TO UL AND
 CSA REQUIREMENTS

APPROVAL RATING :-
 15AMP - 250 V.A.C.
 1/3HP - 125 OR 250 V.A.C.

DIAGRAM OF CONNECTIONS



INSTALLATION DRAWING



23 JAN 2003

1	FIRST ISSUE	18/09/02
ISSUE	REVISION	DATE

saia-burgess

Smart solutions for comfort and safety
 Saia-Burgess Gateshead Limited
 Dukewar, Team Valley Trading Estate
 Gateshead, Tyne & Wear NE11 0UB
 Tel: +44 (0) 191 401 6100
 Fax: +44 (0) 191 401 6322
 www.saia-burgess.co.uk



THIRD ANGLE
 PROJECTION

DO NOT SCALE!
 THIS DRAWING MUST ONLY BE
 AMENDED ON A CAD SYSTEM
 ALL DIMENSIONS SPECIFIED
 IN MILLIMETRES

TOLERANCES UNLESS STATED:

NO DECIMAL PLACES ±0.40
 1 DECIMAL PLACE ±0.15
 2 DECIMAL PLACES ±0.15
 ANGULAR ±1°
 INCH - OUNCE UNITS [IN BRACKETS]

APPROVED

DRAWN	T.BELL	CHECKED BY	<i>[Signature]</i>
DATE	18/09/02	ENGINEERING	<i>[Signature]</i>
SCALE	2/1	QUALITY ASSURANCE	<i>[Signature]</i>

TITLE / DESCRIPTION
VCF9Q2 - UL

Drg No :- C 44607

A3