



Brand of NTN Group

Technical data


CEX206

Insert bearings



Cylindrical outer diameter, fixing by eccentric locking collar, seal with slinger

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
a - Distance to grooves in OR	3,2 mm
b - Groove width in OR	1,9 mm
B - Width of Inner Ring	36,5 mm
B1 - Overall width Inner Ring	48,4 mm
B2 - Width of eccentric locking collar/nut	15,9 mm
C - Width of Outer Ring	19 mm
C1 - Distance center of OR to center of lubrication zone	4,2 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

d - Shaft diameter	30 mm
d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve	44,5 mm
D - Outer diameter of OR	62 mm
G - Set screw size	M6x1
m - Distance to set screw	6 mm
N1 - Groove dia in OR	59,61 mm
r - Radius Inner Ring	1.5
S - Distance front side/bearing centre	18,3 mm
f0 - Factor	13.7
SW - Wrench size	3 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	19500000 mN
C0 - Static load rating	11200000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	0,41 kg
Recommended tightening torque for set screw	5.5 N-m

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	3.56820652173913 Hz
BPFI - Over rolling frequency on inner (60 rpm)	5.43179347826087 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	4.62233110806801 Hz
BRF - Rotational frequency – rolling element (60 rpm)	2.311165554034 Hz



BEARING FREQUENCIES

FTF - Rotational frequency - cage (60 rpm)

0.396467391304348 Hz

