

4-2232979-4 ✓ ACTIVE

GRACE INERTIA | GRACE INERTIA 2.0

TE Internal #: 4-2232979-4

4 Position, Plug, Connector Assembly, Insulation Displacement (IDC), Wire-to-Board, Tin (Sn), Normal, UL 94V-0, GRACE INERTIA 2.0

[View on TE.com >](#)



Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Connector & Housing Type: **Plug**

Mating Retention Type: **Locking Latch**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Contacts Preloaded	Yes
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Connector & Keying Code	B
-------------------------	---



Primary Product Color	Black
-----------------------	-------

Contact Features

Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention Type	Locking Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	2 mm [.079 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Glow Wire Rating	Glow Wire
UL Flammability Rating	UL 94V-0

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)

Candidate List Declared Against: JUNE 2025 (250)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5-2232979-0
SGI2.0 PLUG ASSEMBLY 10P, KEY B, BLK



TE Part # 1-2232979-2
SGI2.0 PLUG ASSEMBLY 2P, KEY A, NTL



TE Part # 1-2232979-4
SGI2.0 PLUG ASSEMBLY 4P, KEY A, NTL



TE Part # 4-2232979-6
SGI2.0 PLUG ASSEMBLY 6P, KEY B, BLK



TE Part # 4-2232979-7
SGI2.0 PLUG ASSEMBLY 7P, KEY B, BLK



TE Part # 4-2232979-2
SGI2.0 PLUG ASSEMBLY 2P, KEY B, BLK



TE Part # 4-2232979-3
SGI2.0 PLUG ASSEMBLY 3P, KEY B, BLK



TE Part # 4-2232979-9
SGI2.0 PLUG ASSEMBLY 9P, KEY B, BLK



TE Part # 4-2336678-4
SGI2.0 RA SMT HDR ASSY 4P, key B, BLK



TE Part # 4-2232979-5
SGI2.0 PLUG ASSEMBLY 5P, KEY B, BLK


Also in the Series | GRACE INERTIA 2.0



Connector Contacts(6)



Connector Hardware(9)



PCB Headers & Receptacles(70)




Rectangular Connector Housings(22)




Rectangular Power Connectors(1)



Standard Rectangular Connectors(40)



Wire-to-Board Connector Assemblies & Housings(40)



Wire-to-Board Headers & Receptacles (70)

Customers Also Bought



TE Part #T4111012041-000
M12 M, 4P GOLD A_CODE S
SHIELDED PG9



TE Part #1SNA199420R2100
BADRL



TE Part #52924
TERMINAL,PIDG SPR SPD 26-22 6




TE Part #165008
PLASTI-GRIP, SPADE 22-16 8



TE Part #1-1622561-0
LR1 1% 732R




TE Part #1622700-1
LR2 1% 1K0




TE Part #2-1658526-9
609-1630LF=FSKT IDC S 16 30AU



TE Part #3-2176367-5
RQ 0603 10K5 0.1% 10PPM 1K RL



TE Part #1-2176475-9
RA73F 1J 9K09 0.1% 1K RL



TE Part #AS612-35PN-903M
PLUG BOOT TERMIN'N (903M)



Documents

Product Drawings

[SGI2.0 PLUG ASSEMBLY 4P, KEY B,BLK](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_4-2232979-4_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-2232979-4_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-2232979-4_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[VDE Certificate](#)

English

[VDE Certificate](#)

English