





SITOR fuse holder 22x 127 63 A 1500 V AC/1000 V DC 1-pole

| Model                                                           |                                                                                   |             |
|-----------------------------------------------------------------|-----------------------------------------------------------------------------------|-------------|
| product brand name                                              | SITOR                                                                             |             |
| product designation                                             | SITOR fuse switch disconnecter                                                    |             |
| design of the actuating element                                 | swivel knob                                                                       |             |
| General technical data                                          |                                                                                   |             |
| number of poles                                                 | 1                                                                                 |             |
| size of fuse link                                               | 22x127                                                                            |             |
| utilization category                                            | AC20B/DC20B                                                                       |             |
| size of the fuse link                                           | 22x127 mm                                                                         |             |
| operating voltage                                               | <div><div></div><div>1 500 V</div></div> <div><div></div><div>1 000 V</div></div> |             |
| <div><div></div><div>at AC rated value maximum</div></div>      |                                                                                   |             |
| <div><div></div><div>at DC rated value maximum</div></div>      |                                                                                   |             |
| Protection class                                                |                                                                                   |             |
| protection class IP on the front                                | IP20                                                                              |             |
| Main circuit                                                    |                                                                                   |             |
| operational current rated value                                 | 63 A                                                                              |             |
| Suitability                                                     |                                                                                   |             |
| suitability for use main switch                                 | No                                                                                |             |
| suitability for use switch disconnecter                         | No                                                                                |             |
| suitability for use EMERGENCY OFF switch                        | No                                                                                |             |
| suitability for use safety switch                               | No                                                                                |             |
| Product function                                                |                                                                                   |             |
| product function fuse monitoring                                | No                                                                                |             |
| Short circuit                                                   |                                                                                   |             |
| conditional short-circuit current (I <sub>q</sub> ) rated value | 50 kA                                                                             |             |
| Connections                                                     |                                                                                   |             |
| connectable conductor cross-section solid                       | <div><div></div><div>1 mm²</div></div> <div><div></div><div>50 mm²</div></div>    |             |
| <div><div></div><div>minimum</div></div>                        |                                                                                   |             |
| <div><div></div><div>maximum</div></div>                        |                                                                                   |             |
| type of electrical connection for main current circuit          | screw-type terminals                                                              |             |
| Mechanical Design                                               |                                                                                   |             |
| height                                                          | 200 mm                                                                            |             |
| depth                                                           | 102 mm                                                                            |             |
| fastening method                                                | <div><div></div><div>Yes</div></div> <div><div></div><div>No</div></div>          |             |
| <div><div></div><div>floor mounting</div></div>                 |                                                                                   |             |
| <div><div></div><div>rail mounting</div></div>                  |                                                                                   |             |
| net weight                                                      | 488 g                                                                             |             |
| Approvals Certificates                                          |                                                                                   |             |
| General Product Approval                                        | other                                                                             | Environment |

**Further information****Information on the packaging**<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC2391-0MK>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/3NC2391-0MK>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC2391-0MK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2391-0MK)**CAX-Online-Generator**<http://www.siemens.com/cax>**Tender specifications**<http://www.siemens.com/specifications>



last modified:

4/12/2025 

