


BEP01SBT0 Datasheet

**Product Name // IP67 Polycarbonate BE Series Enclosure
80mm x 53mm x 72 mm Black Base Transparent Lid No Lid
Holes**

[View Product Page](#)



// Product Description:

- ⊞ IP67 Sealed Enclosures
- ⊞ Corrosion resistant plastic captive lid fixing screws
- ⊞ Posts and slots for PCB mounting as standard
- ⊞ Two M20 threaded knockouts in base for use with M20 cable glands (available separately)
- ⊞ Choice of material depending on part code prefix: BEA - ABS, BEP - Polycarbonate
- ⊞ All enclosures 80mm wide, 53mm tall. Choice of lengths depending on part code: 01S - 72mm, 02S - 106mm, 03S - 139mm
- ⊞ Choice of base colour depending on 7th character of part code: B - Black, G - Grey
- ⊞ Choice of lid colour depending on 8th character of part code: B - Black, G - Grey, Y - Yellow, T - Transparent
- ⊞ Choice of pre-drilled 22mm holes in lid for use with standard switches and indicators, depending on part code suffix:
 - ⊞ 0 - No holes in lid
 - ⊞ 1 - 72mm enclosure has one lid hole, 106mm enclosure has two lid holes, 139mm enclosure has three lid holes
- ⊞ Accessories available separately in choice of black or grey:
 - ⊞ Combifoot DIN rail mounting accessory, for TS32, TS35 rails (part codes BE123456, BE123457)
 - ⊞ Wall mounting accessory (part codes BE123458, BE123459)
 - ⊞ M20 cable glands for cable 3.5mm - 8mm diameter (part codes BE123460, BE123461)

// General Information:

Product Display Title:	IP67 Sealed Enclosures
Product Family:	BE Enclosures
Product Series:	BE Enclosure Accessories
Be Enclosure Size:	80 x 72 x 53mm
Body Material:	Polycarbonate (PC)
Enclosure Base Colour:	Black
Enclosure Lid Colour:	Transparent Lid
Flamability Rating:	UL94V-0
Function:	Small Size Enclosure
Ip Rating:	IP67
Max Operating Temperature:	+100°C
Min Operating Temperature:	-20°C
Number Of Lid Holes:	No Lid Holes

// Product PDF Links

[Enclosures product data](#)

// Product 3D CAD Model Links

[BEP01SBT03D CAD Model](#)