




**Part Number :** [2041020609](#)  
**Product Description :** VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable  
**Series Number :** 204102  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[2041020609\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[351500000AS\\_ENG-000.pdf](#)


[351500000AS\\_KOR-000.pdf](#)

[2041020609-001.pdf](#)

[2041020609-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	204102
Description	VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	191128287777

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes

Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PET/PC
Net Weight	7.995/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	8.00mm, 8.50mm
Pitch - Termination Interface	8.00mm, 8.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +110°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Natural, Glow-Wire Capable	<a href="#"><u>2041020209</u></a>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Friction Lock, Natural, Glow-Wire Capable	<a href="#"><u>2041020409</u></a>

### Use with Part(s)

Description	Part Number
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 3 Circuits, Natural	<a href="#"><u>351820390</u></a>
VersaBlade Terminal Position Assurance (TPA) Retainer, 8.50mm Pitch, 3 Circuits, Red	<a href="#"><u>351820392</u></a>
VersaBlade Male Crimp Terminal, 24-22 AWG, Type C	<a href="#"><u>2270288400</u></a>
VersaBlade Female Crimp Terminal, 24-22 AWG, Type C	<a href="#"><u>2270298400</u></a>
VersaBlade Male Crimp Terminals	<a href="#"><u>35745</u></a>

VersaBlade Female Crimp Terminals	<u>35746</u>
VersaBlade Male Crimp Terminals	<u>35747</u>