

Drywall Screwdriver LXT®

DFS251

18V • 0 – 2 500 min⁻¹

Reliable brushless screwdriver for drill bit screws

A brushless screwdriver intended for drill bit screws. An auto-stop and start, ergonomic design and rubberised handle ensure good grip. Precise depth control and a speed of 2 500 min⁻¹, adjustable from the switch. Equipped with an LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Capacity Drywall Screw	5 mm
No load speed	0 - 2500 min ⁻¹
Sound Pressure Level (L _{pA})	75 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,5 - 1,8 kg
Product Dimensions (L x W x H):	237 x 79 x 259 mm
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Driving Shank	1/4 "
Vibration Level, Screwdriving Without Impact	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Screwdriving Without Impact	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- Depth adjustment
- Reversing switch
- Used for hexagonal screws
- Built-in LED light with afterglow function illuminates the work area
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

191L24-0

Autofeed Attachment, 25-55 mm



784415-6

Nutsetter Bit, 8 x 65 mm, M5



784806-1

Magnetic Nutsetter, 10 x 65 mm, 1/4"



821550-0

Makpac case (2)



837805-3

MakPac (2) Inlay



Other

User manual

Parts drawing