



Connectors > Contacts > RF Contacts

RF Contact Style: **Coax**
Contact Type: **Socket**
Number of Positions: **1**
Connector & Contact Terminates To: **Wire & Cable**
Contact Orientation: **Straight**

Features

Product Type Features

RF Contact Style	Coax
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Contact Features

Contact Type	Socket
Contact Orientation	Straight
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Retention	With
Contact Current Rating (Max)	23 A

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JUNE 2024 (241)
SVHC > Threshold:
Pb (.7% in Contact Lead-Copper Alloy)
Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #YA81516F24155P1VA1
PLUG ASSY

TE Part #6162-233-1277
COAX PIN ASSY

TE Part #6162-284-0877
CONT SOC ASSY

TE Part #1-1423154-4
2122DH122NDC890=RLY,MINI,OFF,2

TE Part #ZPF000000000038838
983-7S 08-03 P7

TE Part #2-1617038-2
HMB1201K01P = M39016/22-009P

TE Part #CAT-R21-731072
Bulbous Heat Shrink Boots: Lipped, Straight

TE Part #2320808-1
TECC0026C5



Documents

Product Drawings
COAX SOC ASSY

English

Instruction Sheets
Instruction Sheet (U.S.)

English