

SafeKey Compact Nylon Padlocks

Design

- Ultimate Key Precision - 6 tumbler blades with matching side-milled keys
- Advanced Key Security - 100,000+ key codes with patent-pending linear, low friction lock mechanism
- Smooth key operation reduces friction of inserting and removing key
- Non-conductive body and internal locking components
- Fast identification - color matched keys/locks
- Compact, non-conductive and non-sparking design is ideal for electrical lockout applications



Material

- Glass-reinforced nylon lock body
- Polymer plastic shackle
- Available Colors:
 - Red
 - Yellow
 - Blue
 - Green
 - Black
 - Orange
 - White
 - Purple
 - Brown

| Chemical | °C | Chemical | °C |
|---|-------|---|-------|
| Acetone | 25 | Petroleum | 25 |
| Acetone | 60 | Turpentine oil | 25 |
| Chlorine, chlorine water | 25 | Turpentine substitute (white spirit) | 25 |
| Fuel, engine: Gasoline (normal & premium grade) | 85 | Trichloroethane 1,1,1 | 45 |
| Lubrication oil: gear oil | < 120 | Lubricating oil: HD engine oils, hydraulic oils, transformer oils | < 120 |
| Fuel, engine: M15 mixture (15% methanol) | 70 | Water (including seawater) | 25 |
| Methanol | 25 | Water (including seawater), chlorinated (<0,5 mg/l) | 80 |

Temperature Range

- Service Temperature: -26° to 121°C (-15° to 250°)


Chemical Resistance

All approved chemicals listed are based on the manufacturers specified chemical resistance chart for plastic material only.

Dimensions

List dimensions with appropriate labels:

| | | |
|-----|---|---------------------|
| "A" | - | 1.25 in [32 mm] |
| "B" | - | 1.7 in [43 mm] |
| "C" | - | 0.75 in [19 mm] |
| "D" | - | 1.0 in [25.4 mm] |
| "E" | - | Ø0.186 in [Ø4.7 mm] |



Warranty

Note: All values shown are averages and should not be used for specification purposes. Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information. Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties expressed or implied, and assumes no liability in connection with the use of this information.

Catalog Numbers

| Compact Nylon Lock - 0.98 in (25 mm) Shackle | | | |
|--|--------------------------|--------------------------|------------------------------|
| 1 Padlock - Keyed Different | 3 Padlocks - Keyed Alike | 6 Padlocks - Keyed Alike | 6 Padlocks - Keyed Different |
| CPT-BLK-25PL-KD | CPT-BLK-25PL-KA3PK | CPT-BLK-25PL-KA6PK | CPT-BLK-25PL-KD6PK |
| CPT-BLU-25PL-KD | CPT-BLU-25PL-KA3PK | CPT-BLU-25PL-KA6PK | CPT-BLU-25PL-KD6PK |
| CPT-BRN-25PL-KD | CPT-BRN-25PL-KA3PK | CPT-BRN-25PL-KA6PK | CPT-BRN-25PL-KD6PK |
| CPT-GRN-25PL-KD | CPT-GRN-25PL-KA3PK | CPT-GRN-25PL-KA6PK | CPT-GRN-25PL-KD6PK |
| CPT-ORG-25PL-KD | CPT-ORG-25PL-KA3PK | CPT-ORG-25PL-KA6PK | CPT-ORG-25PL-KD6PK |
| CPT-PRP-25PL-KD | CPT-PRP-25PL-KA3PK | CPT-PRP-25PL-KA6PK | CPT-PRP-25PL-KD6PK |
| CPT-RED-25PL-KD | CPT-RED-25PL-KA3PK | CPT-RED-25PL-KA6PK | CPT-RED-25PL-KD6PK |
| CPT-WHT-25PL-KD | CPT-WHT-25PL-KA3PK | CPT-WHT-25PL-KA6PK | CPT-WHT-25PL-KD6PK |
| CPT-YLW-25PL-KD | CPT-YLW-25PL-KA3PK | CPT-YLW-25PL-KA6PK | CPT-YLW-25PL-KD6PK |

MSDS Information

1. HAZARDS IDENTIFICATION

This product is NOT DANGEROUS and contains no hazardous ingredients.

2. FIRST AID MEASURES/HEALTH INFORMATION /PROTECTION

| | |
|----------------------|--|
| Eye Contact: | Not applicable, product is inert |
| Ingestion: | Not applicable, first aid is not normally required. |
| Inhalation: | Not applicable |
| Skin Contact: | Not applicable, product is inert, except if product is melted use gloves. For hot melted product, immerse in or flush affected area with water to dissipate heat, and then obtain medical attention. |
| Exposure Limits: | None |
| Threshold Limits | None |
| Personal Protection: | None (ambient conditions) |
| NPCA-HMIS Rating: | Health: 0; Flammability: 1; Reactivity: 0 |
| NFPA-704 Rating: | Health: 0; Flammability: 1; Reactivity: 0 |

3. FIRE-FIGHTING MEASURES

| | |
|--|--|
| <ul style="list-style-type: none"> Be cautious of hot melted Nylon | <ul style="list-style-type: none"> Use water spray to cool fire, exposed surfaces, and to protect personnel |
| <ul style="list-style-type: none"> Isolate product from fire | <ul style="list-style-type: none"> Respiratory and eye protection is required for fire fighting personnel |
| <ul style="list-style-type: none"> Extinguish fire with water spray | <ul style="list-style-type: none"> Decomposition products under fire conditions: Oxygen-lean conditions may cause monoxide and irritating smoke |

4. ACCIDENTAL RELEASE MEASURES

| | |
|-------|---|
| Land | Recover material and place in suitable container for reuse or for disposal in conformance with local regulations. |
| Water | Recover material and place in suitable container for reuse or for disposal in conformance with local regulations. |

5. HANDLING AND STORAGE

| | |
|---|--|
| 5.1 Handling | 5.2 Storage |
| No precautions noted - see local regulation if needed | Storage Pressure: Atmospheric |
| | Storage Temperature: Ambient, no direct sunlight |

6. EXPOSURE CONTROLS/PERSONAL PROTECTION

| | |
|---------------------------|--|
| 6.1 Exposure Limit Values | 6.2 Exposure Controls |
| None | 6.2.1 Occupational Exposure Controls |
| | 6.2.1.1 Respiratory Protection: Not applicable |
| | 6.2.1.2 Hand Protection: Not applicable |
| | 6.2.1.3 Eye Protection: Not applicable |
| | 6.2.1.4 Skin Protection: Not applicable |
| | 6.2.2 Environmental Exposure Controls: No data available |

7. PHYSICAL AND CHEMICAL PROPERTIES

| | |
|---------------------|--|
| General Information | |
| Other Information | |

8. STABILITY AND REACTIVITY

| |
|---|
| 8.1 Conditions to Avoid |
| Higher Temperatures and direct sunlight (chemical resistance is excellent) |
| Highly stable, but temperatures over 480 F may cause degradation |
| 8.2 Materials to Avoid |
| No data available |
| 8.3 Hazardous Decomposition Products |
| Under fire and oxygen-lean conditions may cause monoxide and irritating smoke |

9. ECOLOGICAL INFORMATION

| | |
|-----------------------------------|-------------------|
| 9.1 Ecotoxicity | No data available |
| 9.2 Mobility | No data available |
| 9.3 Persistence and Degradability | No data available |
| 9.4 Bioaccumulative Potential | No data available |
| 9.5 Other Adverse Effects | No data available |

10. DISPOSAL CONSIDERATIONS

| |
|--|
| None of the materials in this product are Recyclable, dispose of all materials in accordance with an applicable federal, state, and local law. |
|--|

11. TRANSPORT INFORMATION

| |
|-------------------|
| No data available |
|-------------------|

12. REGULATORY INFORMATION

| | |
|---|----------------------|
| This product has been tested and validated to the Regulatory Requirements listed below: | |
| • OSHA 29 CFR 1910.147 ©(4)(ii)(A)(1)/(c)(5)(ii)(C)(1) | • ANSI Standard Z244 |

13. OTHER INFORMATION

| |
|-------------------|
| No data available |
|-------------------|