

K10P-11A55-120

! PENDING OBSOLESCENCE

Potter & Brumfield | Potter & Brumfield K10

TE Internal #: 4-1393144-6

TE Internal Description: K10P-11A55-120=K10/K20

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 3-1393144-3
K10P-11AT5-120=K10/K20




TE Part # 2-1393144-2
K10L-11A55-120=K10/K20

Also in the Series | **Potter & Brumfield K10**




AC Relays(7)



General Purpose Power Relays(18)



PCB Relays(4)




Relay Accessories(3)

Customers Also Bought



TE Part #1-640551-6
16P MTA156 COVER



TE Part #3-641215-2
02P MTA100 HDR ASSY FL/ST 30AU



TE Part #206306-5
CPC RECEPT ASSEMBLY SIZE 23-37




TE Part #207365-7
METRIMATE PIN HEADER ASSY,3P




TE Part #207359-1
RECEPT HSG,3 POSN,METRIC




TE Part #5-1393144-7
K10P-11D15-24=K10/K20



TE Part #225686-E
POWELM BUCHSE VOLLM M10 11
2,54 * EP 17,



TE Part #CAT-104MTA-NYLCC
Nylon PCB Connector Covers: 2.54
mm, MTA 100



TE Part #745230-2
20DF SOCKET CONTACT,PLATED



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1393144-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1393144-6_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1393144-6_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

K10 Series Miniature Relay

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English