



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**  
Mating Tab Width: **4.75 mm [ .187 in ]**  
Mating Tab Thickness: **.81 mm [ .032 in ]**  
Magnet Wire Size: **.16 – 1.02 mm**

Features

Product Type Features

|                                    |                    |
|------------------------------------|--------------------|
| Compatible With Discrete Wire Type | Magnet Wire, Solid |
|------------------------------------|--------------------|

Contact Features

|                               |                  |
|-------------------------------|------------------|
| Magnet Wire Terminal Type     | Tab              |
| Mating Tab Width              | 4.75 mm[.187 in] |
| Mating Tab Thickness          | .81 mm[.032 in]  |
| Terminal Plating Material     | Tin              |
| Contact Underplating Material | Copper           |
| Terminal Orientation          | Straight         |

Termination Features

|                                    |                               |
|------------------------------------|-------------------------------|
| Termination Method to Wire & Cable | Insulation Displacement (IDC) |
|------------------------------------|-------------------------------|

Mechanical Attachment

|                       |       |
|-----------------------|-------|
| Mating Retention Type | Barbs |
|-----------------------|-------|

Dimensions

|                 |                  |
|-----------------|------------------|
| Terminal Height | 6.17 mm[.243 in] |
|-----------------|------------------|



|                                    |                  |
|------------------------------------|------------------|
| Magnet Wire Size                   | .16 – 1.02 mm    |
| Stock Thickness (Magnet Wire Side) | .5 mm[.02 in]    |
| Product Length                     | 12.5 mm[.492 in] |

Usage Conditions

|                   |             |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

Operation/Application

|                                    |        |
|------------------------------------|--------|
| Compatible With Wire Base Material | Copper |
|------------------------------------|--------|

Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1601434  
531-1952=POCKET SPECIFICATION

TE Part # 2-1601243-2  
TAB,.118 X .020,STD,SMZ

TE Part # 4-1601112-2  
TAB,110X032,STD SMZ WITH MULTI-BARB

Also in the Series | SIAMEZE

Insertion & Extraction Tools(1)

Magnet Wire Terminals(191)

Customers Also Bought

TE Part #1622826-2  
CRG0402 5% 100K

TE Part #1622826-4  
CRG0402 5% 10K

TE Part #6-1625868-9  
RP 2A 0.25W 27R4 0.1% 25PPM 1K RL

TE Part #5767054-1  
MICT,RECPT,38,ASSY,PDNI

Documents

Product Drawings  
TAB,.187 X .032,STD,SIAMEZE  
English  
TAB,.187 X .032,STD,SIAMEZE  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_4-1601058-2\_E.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_4-1601058-2\_E.3d\_igs.zip  
English



Customer View Model

[ENG\\_CVM\\_CVM\\_4-1601058-2\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742\\_HOUSEHOLD\\_APPLIANCES\\_RAST5](#)

English

Magnet Wire Terminals & Splices

English

[1-1773702-7 \\_IDC\\_Magnet\\_Wire](#)

English

Product Specifications

[Application Specification](#)

English