



FAG

32315-B

Tapered roller bearing

Tapered roller bearings 323, main dimensions to DIN ISO 355 / DIN 720, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	PN	Normal (ISO 492:2014)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	B	Increased contact angle
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width, inner ring
C	45 mm	Width, outer ring
T	58 mm	Width, total
C _r	330,000 N	Basic dynamic load rating, radial
C _{0r}	470,000 N	Basic static load rating, radial
C _{ur}	55,000 N	Fatigue load limit, radial
n _G	4,350 1/min	Limiting speed
n _{gr}	3,400 1/min	Thermal speed rating
m	5.636 kg	Weight



Mounting dimensions

$d_{a \max}$	90 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	87 mm	Minimum diameter of shaft shoulder
$D_{a \min}$	124 mm	Minimum diameter of housing shoulder
$D_{a \max}$	148 mm	Maximum diameter of housing shoulder
$D_{b \min}$	151 mm	Minimum diameter of housing shoulder
$C_{a \min}$	7 mm	Minimum axial space
$C_{b \min}$	14 mm	Minimum axial space
$r_{a \max}$	3 mm	Maximum fillet radius of shaft
$r_{b \max}$	2.5 mm	Maximum fillet radius of housing

Dimensions

$r_{1, 2 \min}$	3 mm	Minimum chamfer dimension of inner ring back face
$r_{3, 4 \min}$	2.5 mm	Minimum chamfer dimension of outer ring back face
a	47 mm	Distance between the apexes of the pressure cones
d_1	120.4 mm	Guidance rib diameter of inner ring

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0.55	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y	1.1	Dynamic axial load factor
Y_0	0.6	Static axial load factor

Additional information

T5GD075

Comparative designation to ISO 10317 and ISO 355



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed