


## RS PRO 1.5 mm<sup>2</sup> Flexible Cable, 50 m Length

RS Stock No: 606-070

### FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and enhances durability
- **4 Cores:** Suitable for multi-phase electrical systems
- **Operating Temperature Range:** -15 °C to 70 °C, ensuring reliable performance in various conditions
- **Voltage Rating of 500 V:** Suitable for a wide range of electrical applications
- **Plain Conductor Type:** Ensures ease of installation and connectivity
- **White Jacket Colour:** Ideal for aesthetic installations where visibility is required



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible cable is designed for a wide range of electrical applications, offering reliable performance and durability. With a 1.5 mm<sup>2</sup> cross-sectional area and a length of 50 metres, it is ideal for installations requiring flexibility and ease of handling. The cable's annealed copper conductor ensures excellent conductivity, making it suitable for both domestic and industrial environments.

## General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

## Mechanical Specifications

Cable CSA	1.5 mm <sup>2</sup>
Cable Length	50 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	4
Outside Diameter	10.5 mm

## Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

## Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

## Electrical Specifications

Voltage	500 V
---------	-------