




Connectors > Terminal Blocks & Strips > Barrier Strips



Number of Positions: 8
Barrier Strip Style: Tri-Barrier
Bottom Termination Type: Printed Circuit Pin
Connector System: Wire-to-Board
Centerline (Pitch): 8.26 mm [.325 in]

Features

Product Type Features

Block Style	Flat Bottom
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Levels	1
Number of Positions	8
Number of Rows	1

Electrical Characteristics

Operating Voltage	150 V, 300 V
-------------------	--------------

Body Features

Product Orientation	Right Angle
Barrier Strip Style	Tri-Barrier

Contact Features

Contact Current Rating (Max)	20 A
------------------------------	------

Termination Features

Bottom Termination Type	Printed Circuit Pin
-------------------------	---------------------

Mechanical Attachment

--	--



Top Termination Type	Wire Clamp Combo Head
Mounting Options	None
Thread Size	4-40
Screw Head Type	Wire Clamp Combo Head
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	8.26 mm[.325 in]
--------------------	------------------

Dimensions

Product Length	67.58 mm[2.66 in]
Wire Size	12 – 22 AWG

Usage Conditions

Operating Temperature Range	0 – 105 °C[32 – 221 °F]
-----------------------------	-------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Package
Packaging Quantity	150

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Buchanan 4 Series



Barrier Strips(47)

Customers Also Bought



TE Part #2414-002-1886
LOCKWASHER, SIZE 18, HDP



TE Part #1-640454-2
12P MTA100 HDR ASSY SQ STR POL




TE Part #1375820-5
CST-100 II HOUSING 5 POS



TE Part #292133-3
CT P/HDR ASSY BOX V 3P W/O KIN




TE Part #2-31880-1
PIDG R 22-16 COMM 22-18 MIL 4





TE Part #3-640601-4
04P MTA156 CONN ASSY 22AWG LF



TE Part #5520425-3
MJ,TE,6P/6C,BULK PAC



TE Part #3-641437-4
04P MTA156 PSTD CONN ASSY RED



Documents

Product Drawings

4PCR-08-006=4PCR ASSEMBLY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-1437648-8_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-1437648-8_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-1437648-8_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE

English

Agency Approvals

UL

English