



### Main

Range of product	Prodis Acti 9 Clario Librio
Product or component type	Shunt trip release with OC contact
Device short name	MX + OF
Signal contacts composition	1 C/O
[Ie] rated operational current	3 A at 415 V AC 6 A at <= 240 V AC
[Uc] control circuit voltage	100...415 V AC 50/60 Hz 110...130 V DC
9 mm pitches	2

### Complementary

Range compatibility	Acti 9 iDPN Acti 9 C120 Acti 9 C40 Acti 9 C60H-DC Acti 9 C60NA-DC Acti 9 C60PV-DC Acti 9 DPN Vigi Acti 9 DT40 Acti 9 DT60 Acti 9 ID C40 Acti 9 IDc Acti 9 ITG40 Acti 9 ID Acti 9 DPN
Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net weight	65 g
Colour	White
Connections - terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm <sup>2</sup> - rigid
Wire stripping length	9 mm for bottom connection
Tightening torque	1 N.m bottom
Compatibility code	MX + OF

### Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASTA ASEFA LCIE KEMA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Package 1 Weight	70 g
Package 2 Weight	624 g
Package 3 Weight	6.103 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------