

Product data sheet

Specifications



Repacked, add-on residual current device, Acti9 Vigi C120, 4P, 125A, A-SI type, selective, 300mA, 230...415VAC

A9N18560W



This repacked option saves 4.650 over the standard condition

Main

Range	Acti9
Product name	Acti9 Vigi C120
Product or component type	Add-on residual current device
Device short name	Vigi C120
Poles description	4P
[In] rated current	125 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Selective
Earth-leakage protection class	Type A-SI (Super Immunised)
Standards	EN 61009 IEC/EN 61009-2-1

Complementary

Device location in system	Outgoer Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	230...415 V AC 50 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail
Electrical connection to mcb	By screws
9 mm pitches	10
Height	95 mm
Width	198 mm
Depth	73 mm
Product weight	0.58 kg
Colour	White

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical durability	20000 cycles
Connections - terminals	Tunnel type terminals 1...35 mm² flexible Tunnel type terminals 1...50 mm² rigid
Wire stripping length	15 mm
Tightening torque	3.5 N.m

Environment

IP degree of protection	IP20
Pollution degree	3 conforming to IEC 60947-2
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	13.5 cm
Package 1 Length	25.1 cm
Package 1 Weight	658.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.752 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

5 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A7b24ae6-2312-4e67-b7c9-56fce3e8c723

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins