


BZV03/A0620/75 Datasheet

 [View Product Page](#)

Product Name // Vertical Power Entry Module 78.7mm C14
Cold Condition Inlet (PX0575) 6.3mm Tab Termination A0620
Filter (6A PS01/A L/C v2) 2 x FX0359 Fuseholders Double
Contact Illuminated Switch Marked I/O Green



Panel Thickness: 1.0, 1.5, 2.0, 3.0mm.
BZV03, BZV04/****/** A = 62.5 With Filter
39.0 Without Filter
BZV05, BZV06/****/** A = 39.0

// **Product Description:**

- Vertical Power Entry Module 50.8mm/78.7mm
 - C14 Cold Condition Inlet (PX0575)
 - Choice of Termination depending on part code:
 - Part codes prefixed BZV03: 6.3mm Tab
 - Part codes prefixed BZV04: 2.8mm Tab
- Choice of mains filter depending on part code:
 - Part codes containing /Z0000 are unfiltered
 - Choice of mains filter options (part codes containing codes starting /A)
 - Choice of many other options as specified by individual part code, including fuseholders, voltage selectors, indicators, illuminated switches, switch markings, etc
 - Also available in C16 Hot Condition Inlet (PX0595) versions in both Terminations (6.3mm Tab part code BZV05, 2.8mm Tab part code BZV06), Unfiltered only

// **General Information:**

Product Display Title:	Vertical Power Entry Module 50.8mm/78.7mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	6A
Filter Type:	6A PS01/A L/C v2
Function:	C14 Inlets
iec Connector Components:	None
iec Connector Mates With:	PX0575
iec Filter Options:	A0620
iec Neon Colour:	Green
iec Vertical Module Height:	78.7mm
Inlet Type:	C14 Cold Condition Inlet
Number Of Fuseholders:	2 x FX0359 Fuseholders
Switch Type:	Double Contact Marked I/O Illuminated
Voltage Max:	250V

// **Product PDF Links**

 [Power Entry Modules product data](#)

// **Product 3D CAD Model Links**

 [BZV03/A0620/753D CAD Model](#)